

# PXM6011/04S/CR/0405/SN Datasheet

**Product Name // Inline Cable Connector PXM6011 Series 4**

**Contact Socket Crimp/Solder Termination (contacts available separately) 4mm-5mm Cable (Dark Grey Gland)**

**Metal Body With Braid Termination**

[View Product Page](#)



## // Product Description:

- ⊞ Inline Cable Connectors
- ⊞ Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
- ⊞ 30 degree push twist locking, tamperproof lock prevents accidental un-mating
- ⊞ Socket
- ⊞ 4 Contacts
- ⊞ Crimp/solder termination with contacts and fitting tool available separately
- ⊞ Metal Body With Braid Termination
- ⊞ Cable acceptance 4mm-5mm diameter
- ⊞ Gland Pack PXP6088 available separately to accommodate all sizes
- ⊞ PXM6082 Sealing Cap available separately to maintain IP rating of unmated connectors
- ⊞ Mate with PXM6010 Series Flex Connectors

## // General Information:

Product Display Title:	Inline Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Body Colour:	Metallic Grey
Body Material:	Brass
Body Material Type:	Metal Body With Braid Termination
Contact Type:	Socket Contact
Coupling Type:	Push-Twist
Current Max:	10A, 4A, 7A
Diameter Over Coupling Ring Mm:	32mm
Function:	Inline Cable Connector
Insulation Resistance:	>10 <sup>6</sup> MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	5mm
Min Cable Entry Size:	4mm
Max Contact Accommodation Awg:	20AWG
Min Contact Accommodation Awg:	16AWG
Max Contact Accommodation Mm2:	1.5mm <sup>2</sup>
Min Contact Accommodation Mm2:	0.5mm <sup>2</sup>
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	4 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-11 Test Ka Salt Mist
Voltage Max:	277V

### // Product PDF Links

[6000 Series power connectors...](#)

[6000 Series metal body power...](#)

### // Product 3D CAD Model Links

[PXM6011/04S/CR/0405/SN3D CAD Model](#)



Have a question or project enquiry you'd like to talk to us about?

[Click Here To Contact Us](#)