



Part Number : [2244511112](#)

Product Description : Pre-Crimped Lead Stac64 Female-to-Stac64 Female, Tin (Sn) Plating, 150.00mm Length, 0.75mm² Wire, Black

Series Number : 224451

Status : Active

Product Category : Power and Signal Cable Assemblies




Documents & Resources

Drawings

[Drawing 2244511112_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224451
Description	Pre-Crimped Lead Stac64 Female-to-Stac64 Female, Tin (Sn) Plating, 150.00mm Length, 0.75mm ² Wire, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Stac64 Crimp Terminals
Product Family	Off-the-Shelf Pre-Crimped Leads
Product Name	Stac64
UPC	196823398186

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	14V DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.806/g
Number of Rows	1
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression

Wire/Cable Type	FLRY-B
Wire Insulation Diameter	1.80mm
Wire Size mm ²	0.75

This document was generated on Sep 28, 2023