




P	LTR	DESCRIPTION	DATE	DWN	APVD
A		NEW DRAWING	07SEP2022	BDA	DH
AI		MATERIAL INFO. UPDATED	02NOV2022	BDA	DH




4 X Ø5 THRU ALL
 $\sqrt{\text{Ø } 8.30 \times 90^\circ}$

4 X NICKEL/COPPER FABRIC
 CONDUCTIVE STRIP

1 LAYER 3.18 CELL X 6.35 THK
 ALUMINIUM 5052 HONEYCOMB
 SURTEC 650 FINISH

GENERAL TOLERANCES:
 LINEAR: ± 0.8
 HOLE CENTRES: ± 0.5
 ANGULAR: $\pm 0.5^\circ$

THE VENT BODY DESIGN
 & OBSTRUCTED AREA
 MAY VARY



ISOMETRIC VIEW (NTS)

HIGH IMPACT ABS	KEMVENT60	2430085-1
MATERIAL	ALIAS PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASAVARAJA D A 07SEP2022	TE Connectivity	
DIMENSIONS: mm		CHK B SELVAPANDIAN 07SEP2022	NAME KEM_1651-KEMVENT_60	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D HEMMINGS 07SEP2022	PRODUCT SPEC	
0 PLC \pm		APPLICATION SPEC		
1 PLC ± 0.1		WEIGHT		
2 PLC ± 0.07		SCALE 2:1 SHEET 1 OF 1 REV AI		
3 PLC ± 0.001		RESTRICTED TO		
4 PLC ± 0.0001		SIZE CAGE CODE DRAWING NO		
ANGLES \pm		A2 00779 C-KEM_1651-KEMVENT_60		
FINISH		CUSTOMER DRAWING		
MATERIAL SEE TABLE				