

## RF TERMINATION

### Type 6500\_N-50-1/199\_N

## Description

Precision Termination, Low Power



## Product Configuration

Connector	N-precision plug (male)
Interface standards	IEC 60169-16_MIL-STD-348A/304_CECC 22210

## Technical Data

### Electrical Data

Nominal Impedance	50 Ω			
Frequency range	0 to 18 GHz			
Frequency sub range	DC to 4 GHz	4 to 8 GHz	8 to 12.4 GHz	12.4 to 18 GHz
VSWR max.	1.03	1.04	1.05	1.06
Power rating	2 Watt average power up to 25 °C ambient temperature, linearly derated to 1 Watt at 125 °C ambient temperature. 1000 Watt peak power , 5 μs pulse, 0.05 % duty cycle			

### Mechanical Data

Weight	0.057 kg
--------	----------

### Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

### Material Data

Piece Part	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Coupling nut	Stainless Steel	Passivated (Plating)

## Related Documents

Outline drawing	DOU-00120720
-----------------	--------------

## Ordering Information

Single Packaging	6500_N-50-1/199_NE
Packaging	