

Coaxial Cable Connector 11_MMPX-50-2-1/111_N

Description

Straight cable plug

Interface standards

HUBER+SUHNER MMPX STD (Patent US 7.294.023)



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	67 GHz		
Frequency range	DC to 26.5 GHz	26.5 to 50 GHz	50 to 67 GHz
Return loss	25 dB	25 dB	25 dB

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0002 kg

Environmental Data

Operating temperature	-65 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating

Related Documents

Outline drawing	DOU-00056825
Assembly instruction	DOC-0000236402

Ordering Information

Single package	11_MMPX-50-2-1/111_NE
----------------	-----------------------

Additional Information

Suitable cables	EZ_86_TP_M17, EZ_86_AL_TP_M17, SUCOFORM_86, STORM_SR_86
-----------------	---

Remarks

Decoupling tool MMPX shall be used (74_Z-0-0-491/74_Z-0-0-555)!