


## Coaxial Panel Connector 23\_BMA-N50-0-16/119\_N

### Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-33\_MIL-STD-348/321 fully intermateable



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Number of matings	1000
Weight	0.0036 kg

#### Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Stainless Steel	
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00308860
Catalogue drawing	DCA-00321890

### Ordering Information

Single package	23_BMA-N50-0-16/119_NE
----------------	------------------------