




Part Number : [2147205010](#)

Product Description : Zero-Hachi Crimp Terminal, Female, Gold (Au) Plating, 28-30 AWG, Reel

Series Number : 214720

Status : Active

Product Category : Crimp Terminals



Documents & Resources

Drawings

[Drawing 2147205010_sd.pdf](#)

3D Models and Design Files

[3D Model 2147205010_stp.zip](#)

Specifications

[Product Specification 2147190000-PS-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	214720
Description	Zero-Hachi Crimp Terminal, Female, Gold (Au) Plating, 28-30 AWG, Reel
Application	Signal, Wire-to-Board
Product Family	Zero-Hachi Connector System
Product Name	Zero-Hachi
UPC	196823391019

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Durability (mating cycles max)	20
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	4.090/mg
Packaging Type	Reel
Plating min - Mating	1.000µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.50-0.60mm
Wire Size (AWG)	28, 30
Wire Size mm ²	0.04-0.08

Use with Part(s)

Description	Part Number
Zero-Hachi Single Row Receptacle Housings	<u>214719</u>

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Applicator for Zero-Hachi Female Crimp Terminals, 28-32 AWG, UL 3767 Wire	<u>2130693600</u>
FA2 Pneumatic Feed Applicator for Zero-Hachi Female Crimp Terminals, 28-32 AWG, UL 3767 Wire	<u>2130693610</u>
