


# LM3S800 Microcontroller



## Product Features

### 32-Bit RISC Performance

- 32-bit ARM® Cortex™-M3 v7M architecture optimized for small-footprint embedded applications
- 50-MHz operation
- System timer (SysTick) provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism
- Thumb®-compatible Thumb-2-only instruction set processor core for high code density
- Integrated Nested Vectored Interrupt Controller (NVIC) provides deterministic interrupt handling
- 21 interrupt channels with eight priority levels
- Memory protection unit (MPU)
- Unaligned data access enables data to be efficiently packed into memory
- Atomic bit manipulation (bit-banding) delivers maximum memory utilization and streamlined peripheral control

### On-Chip Memory

- 64 KB single-cycle flash with two forms of flash protection on a 2-KB block basis
- 8 KB single-cycle SRAM

### General-Purpose Timers

- Three General-Purpose Timer Modules (GPTM), each configurable as one 32-bit or two 16-bit timers
- Real-Time Clock (RTC) capability

### Watchdog Timer

- 32-bit down counter with a programmable load register
- Separate watchdog clock with an enable
- Programmable interrupt generation logic with interrupt masking
- Lock register protection from runaway software
- Reset generation logic with an enable/disable

### Synchronous Serial Interface (SSI)

- Programmable interface operation for Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces

- Master or slave operation

### UART

- Two fully programmable 16C550-type UARTs
- Separate 16x8 transmit (TX) and 16x12 receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable baud-rate generator with fractional divider

### Analog Comparators

- Three independent integrated analog comparators
- Configurable for output to: drive an output pin or generate an interrupt
- Compare external pin input to external pin input or to internal programmable voltage reference

### Inter-Integrated Circuit (I<sup>2</sup>C) Interface

- Master and slave receive and transmit operation with transmission speed up to 100 Kbps in Standard mode and 400 Kbps in Fast mode
- Interrupt generation
- Master with arbitration and clock synchronization, multimaster support, and 7-bit addressing mode

### GPIOs

- 8-36 GPIOs, depending on configuration
- 5-V-tolerant input/outputs
- Programmable interrupt generation
- Programmable drive strength and slew-rate control

### Power

- On-chip Low Drop-Out (LDO) voltage regulator, with programmable output user-adjustable from 2.25 V to 2.75 V
- Low-power options on controller: Sleep and Deep-sleep modes
- Low-power options for peripherals: software controls shutdown of individual peripherals
- User-enabled LDO unregulated voltage detection and automatic reset
- 3.3-V supply brown-out detection and reporting via interrupt or reset

### Flexible Reset Sources

- Power-on reset (POR)
- Reset pin assertion
- Brown-out (BOR) detector alerts to system power drops
- Software reset
- Watchdog timer reset
- Internal low drop-out (LDO) regulator output goes unregulated

### Additional Features

- Programmable clock source control
- Clock gating to individual peripherals for power savings
- IEEE 1149.1-1990 compliant Test Access Port (TAP) controller
- Debug access via JTAG and Serial Wire interfaces
- Full JTAG boundary scan

# LM3S800 Microcontroller




## Package and Temperature

- 48-pin RoHS-compliant LQFP package
  - Industrial-range (-40°C to +85°C)
  - Extended-range (-40°C to +105°C)

## Target Applications

- Factory automation and control
- Industrial control power devices
- Building and home automation
- Stepper motors
- Brushless DC motors
- AC induction motors



## Ordering Information

Orderable Part Number	Description
LM3S800-IQN50	Stellaris® LM3S800 Microcontroller Industrial Temperature
LM3S800-IQN50(T) <sup>a</sup>	
LM3S800-EQN50	Stellaris® LM3S800 Microcontroller Extended Temperature
LM3S800-EQN50(T)	

a. T= Tape and Reel.

## Development Kit

The Luminary Micro Stellaris™ Family Development Kit provides the hardware and software tools that engineers need to begin development quickly. Ask your Luminary Micro distributor for part number . See the Luminary Micro website for the latest tools available.



Tools to begin development quickly

Luminary Micro, Inc. • 108 Wild Basin, Suite 350 • Austin, TX 78746  
 Main: +1-512-279-8800 • Fax: +1-512-279-8879 • <http://www.luminarymicro.com>

Copyright © 2007-2008 Luminary Micro, Inc. All rights reserved. Stellaris, Luminary Micro, and the Luminary Micro logo are registered trademarks of Luminary Micro, Inc. or its subsidiaries in the United States and other countries. ARM and Thumb are registered trademarks and Cortex is a trademark of ARM Limited. Other names and brands may be claimed as the property of others.

