

2383445-3 ✓ ACTIVE

PowerTube | PowerTube 1000

TE Internal #: 2383445-3

Automotive Terminals, Socket, Pin Diameter 10 mm [.393 in], 00

AWG Wire Size, 70 mm² Wire Size, Locking Clean Body, PowerTube 1000

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals



Terminal Type: **Socket**

Mating Pin Diameter: **10 mm [.393 in]**

Terminal Transmits: **100+ A (Very High Power)**

Wire Size: **70 mm²**

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Terminal Type	Socket
Mating Pin Diameter	10 mm [.393 in]
Interface Plating	Silver (Ag)

Termination Features

Product Terminates To	Wire
-----------------------	------

Dimensions

Wire Size	70 mm ²
Wire Size Search	0 AWG

Usage Conditions

Operating Temperature (Max)	140 °C [284 °F]
-----------------------------	-----------------



Operating Temperature Range -40 – 140 °C[-40 - 284 °F]

Operation/Application

Compatible With Wire Base Material Copper

Other

Terminal Transmits 100+ A (Very High Power)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUL 2021 (219)
 Does not contain REACH SVHC

Halogen Content Not Yet Reviewed for halogen content

Solder Process Capability Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | PowerTube 1000





Automotive Terminals(3)



Other Automotive Connector Accessories(6)

Customers Also Bought




TE Part #1897009-2
TIMER, CONNECTOR HOUSING



TE Part #HDP24-24-21PN-L017
REC, 21P, BLK, N, RNG, 12/16, P



TE Part #4-2098541-1
3POS, MCON 1.2 CB REC 2p TL SEALED



TE Part #962954-1
4MM BUCHS-KONTAKT



TE Part #284848-2
12 POS MCP HYBRID FEMALE CONN



TE Part #2394085-2
Pre-ASSY,Finger Access,Code B



TE Part #2394085-1
Pre-ASSY,Finger Access,Code A



TE Part #9-1452931-9
76POS,MCON 1.2 CB,REC HSG,ASSY, SLD



TE Part #1897014-2
MT-2/JPT SLD 26P PLUG COVER

Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_2383445-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2383445-3_A.3d_igs.zip](#)

2383445-3

Automotive Terminals, Socket, Pin Diameter 10 mm [.393 in], 00 AWG Wire Size, 70 mm² Wire Size, Locking Clean Body, PowerTube 1000



English

Customer View Model

[ENG_CVM_CVM_2383445-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.