

Main switch, P3, 100 A, surface mounting, 3 pole, Emergency switching off function, With red rotary handle and yellow locking ring, Lockable in the 0 (Off) position, in steel enclosure



**Part no. P3-100/SE3/SVB
197370**

General specifications		
Product name		Eaton Moeller® series P3 Main switch
Part no.		P3-100/SE3/SVB
EAN		4015080896746
Product Length/Depth		250 millimetre
Product height		155 millimetre
Product width		200 millimetre
Product weight		2.66 kilogram
Certifications		IEC/EN 60947 IEC/EN 60947-3 VDE 0660 IEC/EN 60204
Product Tradename		P3
Product Type		Main switch
Product Sub Type		None
Catalog Notes		in steel enclosure Rated Short-time Withstand Current (Icw) for a time of 1 second
Features & Functions		
Features		Version as main switch Version as safety switch Version as emergency stop installation Version as maintenance-/service switch
Fitted with:		Red rotary handle and yellow locking ring
Functions		Interlockable Emergency switching off function
Locking facility		Lockable in the 0 (Off) position
Number of poles		Three-pole
General information		
Accessories		Auxiliary contact or neutral conductor fitted by user.
Degree of protection		NEMA 12
Degree of protection (front side)		IP65
Lifespan, mechanical		100,000 Operations
Mounting method		Surface mounting
Mounting position		As required
Operating frequency		1200 Operations/h
Overvoltage category		III
Pollution degree		3
Rated impulse withstand voltage (Uimp)		6000 V AC
Safe isolation		440 V AC, Between the contacts, According to EN 61140
Safety parameter (EN ISO 13849-1)		B10d values as per EN ISO 13849-1, table C.1
Shock resistance		15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
Suitable for		Ground mounting
Switching angle		90 °
Climatic environmental conditions		
Ambient operating temperature (enclosed) - min		-25 °C
Ambient operating temperature (enclosed) - max		40 °C
Terminal capacities		
Terminal capacity		1 x (1.5 - 25) mm ² , flexible with ferrules to DIN 46228 2 x (2.5 - 10) mm ² , solid or stranded 2 x (1.5 - 6) mm ² , flexible with ferrules to DIN 46228 1 x (2.5 - 35) mm ² , solid or stranded

Tightening torque		3 Nm, Screw terminals
Electrical rating		
Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)		760 A
Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)		740 A
Rated breaking capacity at 500 V (cos phi to IEC 60947-3)		880 A
Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)		520 A
Rated operational current (Ie) at AC-21, 440 V		100 A
Rated operational current (Ie) at AC-23A, 230 V		100 A
Rated operational current (Ie) at AC-23A, 400 V, 415 V		100 A
Rated operational current (Ie) at AC-23A, 500 V		96 A
Rated operational current (Ie) at AC-23A, 690 V		68 A
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V		71 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V		71 A
Rated operational current (Ie) at AC-3, 500 V		65 A
Rated operational current (Ie) at AC-3, 660 V, 690 V		23.8 A
Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms		100 A
Rated operational current (Ie) at DC-23A, 24 V		50 A
Number of contacts in series at DC-23A, 24 V		1
Rated operational current (Ie) at DC-23A, 48 V		50 A
Number of contacts in series at DC-23A, 48 V		2
Rated operational current (Ie) at DC-23A, 60 V		50 A
Number of contacts in series at DC-23A, 60 V		2
Rated operational current (Ie) at DC-23A, 120 V		25 A
Number of contacts in series at DC-23A, 120 V		3
Rated operational power at AC-23A, 220/230 V, 50 Hz		30 kW
Rated operational power at AC-23A, 400 V, 50 Hz		55 kW
Rated operational power at AC-23A, 500 V, 50 Hz		55 kW
Rated operational power at AC-23A, 690 V, 50 Hz		55 kW
Rated operational power at AC-3, 380/400 V, 50 Hz		37 kW
Rated operational power at AC-3, 415 V, 50 Hz		37 kW
Rated operational power at AC-3, 690 V, 50 Hz		37 kW
Rated operational voltage (Ue) at AC - max		690 V
Rated uninterrupted current (Iu)		100 A
Uninterrupted current		Rated uninterrupted current Iu is specified for max. cross-section.
Voltage per contact pair in series		60 V
Short-circuit rating		
Rated conditional short-circuit current (Iq)		4 kA (Load side) 80 kA (Supply side)
Rated short-time withstand current (Icw)		2 kA
Short-circuit protection rating		100 A gG/gL, Fuse, Contacts
Switching capacity		
Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)		950 A
Load rating		1.3 x I# (with intermittent operation class 12, 60 % duty factor) 1.6 x I# (with intermittent operation class 12, 40 % duty factor) 2 x I# (with intermittent operation class 12, 25 % duty factor)
Contacts		
Control circuit reliability		1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)		0
Number of auxiliary contacts (normally closed contacts)		0
Number of auxiliary contacts (normally open contacts)		0
Actuator		
Actuator color		Red
Actuator type		Door coupling rotary drive
Design verification		
10.2.2 Corrosion resistance		Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch disconnecter (EC000216)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Switch disconnecter (ecl@ss10.0.1-27-37-14-03 [AKF060013])

Version as main switch		Yes
Version as maintenance-/service switch		Yes
Version as safety switch		Yes
Version as emergency stop installation		Yes
Version as reversing switch		No
Number of switches		1
Max. rated operation voltage U _e AC	V	690
Rated operating voltage	V	690 - 690
Rated permanent current I _u	A	100
Rated permanent current at AC-23, 400 V	A	100
Rated permanent current at AC-21, 400 V	A	100
Rated operation power at AC-3, 400 V	kW	37
Rated short-time withstand current I _{cw}	kA	2
Rated operation power at AC-23, 400 V	kW	55
Switching power at 400 V	kW	55
Conditioned rated short-circuit current I _q	kA	80
Number of poles		3
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		0
Number of auxiliary contacts as change-over contact		0
Motor drive optional		No
Motor drive integrated		No
Voltage release optional		No
Device construction		Complete device in housing
Suitable for floor mounting		Yes
Suitable for front mounting 4-hole		No
Suitable for front mounting centre		No
Suitable for distribution board installation		No
Suitable for intermediate mounting		No

Colour control element			Red
Type of control element			Door coupling rotary drive
Interlockable			Yes
Type of electrical connection of main circuit			Screw connection
Degree of protection (IP), front side			IP65
Degree of protection (NEMA)			12