

**Main switch, T3, 32 A, flush mounting, 1 contact unit(s), 1 pole,
Emergency switching off function, With red rotary handle and yellow
locking ring, Lockable in the 0 (Off) position**

Part no. T3-1-8200/EA/SVB
066576
EL Number 1417079
(Norway)

General specifications	
Product name	Eaton Moeller® series T3 Main switch
Part no.	T3-1-8200/EA/SVB
EAN	4015080665762
Product Length/Depth	104 millimetre
Product height	74 millimetre
Product width	65 millimetre
Product weight	0.168 kilogram
Certifications	UL CSA CSA-C22.2 No. 60947-4-1-14 VDE 0660 IEC/EN 60947-3 CSA Class No.: 3211-05 IEC/EN 60204 UL Category Control No.: NLRV IEC/EN 60947 CE UL 60947-4-1 CSA-C22.2 No. 94 UL File No.: E36332 CSA File No.: 012528
Product Tradename	T3
Product Type	Main switch
Product Sub Type	None
Catalog Notes	Rated Short-time Withstand Current (Icw) for a time of 1 second
Features & Functions	
Features	Version as maintenance-/service switch Version as emergency stop installation Version as main switch
Fitted with:	Red rotary handle and yellow locking ring
Functions	Emergency switching off function Interlockable
Locking facility	Lockable in the 0 (Off) position
Number of poles	Single-pole
General information	
Degree of protection	NEMA 12
Degree of protection (front side)	IP65
Lifespan, mechanical	500,000 Operations
Mounting method	Flush mounting
Mounting position	As required
Number of contact units	1
Operating frequency	1200 Operations/h
Overvoltage category	III
Pollution degree	3
Rated impulse withstand voltage (Uimp)	6000 V AC
Safe isolation	440 V AC, Between the contacts, According to EN 61140
Safety parameter (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
Shock resistance	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
Suitable for	Front mounting center Branch circuits, suitable as motor disconnect, (UL/CSA)
Switching angle	90 °
Climatic environmental conditions	

Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		50 °C
Ambient operating temperature (enclosed) - min		-25 °C
Ambient operating temperature (enclosed) - max		40 °C
Climatic proofing		Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Terminal capacities		
Terminal capacity		14 - 10 AWG, solid or flexible with ferrule 1 x (0.75 - 4) mm ² , flexible with ferrules to DIN 46228 2 x (1 - 6) mm ² , solid or stranded 2 x (0.75 - 4) mm ² , flexible with ferrules to DIN 46228 1 x (1 - 6) mm ² , solid or stranded
Screw size		M4, Terminal screw
Tightening torque		1.6 Nm, Screw terminals 17.7 lb-in, Screw terminals
Electrical rating		
Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)		260 A
Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)		260 A
Rated breaking capacity at 500 V (cos phi to IEC 60947-3)		240 A
Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)		170 A
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V		23.7 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V		23.7 A
Rated operational current (Ie) at AC-3, 500 V		23.7 A
Rated operational current (Ie) at AC-3, 660 V, 690 V		14.7 A
Rated operational current (Ie) at AC-21, 440 V		32 A
Rated operational current (Ie) at AC-23A, 230 V		32 A
Rated operational current (Ie) at AC-23A, 400 V, 415 V		32 A
Rated operational current (Ie) at AC-23A, 500 V		26.4 A
Rated operational current (Ie) at AC-23A, 690 V		17 A
Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms		25 A
Rated operational current (Ie) at DC-13, control switches L/R = 50 ms		20 A
Rated operational current (Ie) at DC-21, 240 V		1 A
Rated operational current (Ie) at DC-23A, 24 V		25 A
Rated operational current (Ie) at DC-23A, 48 V		25 A
Rated operational current (Ie) at DC-23A, 60 V		25 A
Rated operational current (Ie) at DC-23A, 120 V		12 A
Rated operational current (Ie) at DC-23A, 240 V		5 A
Rated operational current (Ie) star-delta at AC-3, 220/230 V		32 A
Rated operational current (Ie) star-delta at AC-3, 380/400 V		32 A
Rated operational current (Ie) star-delta at AC-3, 500 V		32 A
Rated operational current (Ie) star-delta at AC-3, 690 V		25.5 A
Rated operational power at AC-3, 380/400 V, 50 Hz		11 kW
Rated operational power at AC-3, 415 V, 50 Hz		11 kW
Rated operational power at AC-3, 500 V, 50 Hz		15 kW
Rated operational power at AC-3, 690 V, 50 Hz		11 kW
Rated operational power at AC-23A, 220/230 V, 50 Hz		7.5 kW
Rated operational power at AC-23A, 400 V, 50 Hz		15 kW
Rated operational power at AC-23A, 500 V, 50 Hz		15 kW
Rated operational power at AC-23A, 690 V, 50 Hz		15 kW
Rated operational power star-delta at 220/230 V, 50 Hz		7.5 kW
Rated operational power star-delta at 380/400 V, 50 Hz		15 kW
Rated operational power star-delta at 500 V, 50 Hz		18.5 kW
Rated operational power star-delta at 690 V, 50 Hz		22 kW
Rated uninterrupted current (Iu)		32 A
Uninterrupted current		Rated uninterrupted current Iu is specified for max. cross-section.
Short-circuit rating		
Rated conditional short-circuit current (Iq)		1 kA

Rated short-time withstand current (I _{cw})	0.65 kA 650 A, Contacts, 1 second
Short-circuit current rating (basic rating)	5 kA, SCCR (UL/CSA) 40A, max. Fuse, SCCR (UL/CSA)
Short-circuit current rating (high fault)	40 A, Class J, max. Fuse, SCCR (UL/CSA) 10 kA, SCCR (UL/CSA)
Short-circuit protection rating	35 A gG/gL, Fuse, Contacts
Switching capacity	
Load rating	1.6 x I _# (with intermittent operation class 12, 40 % duty factor) 1.3 x I _# (with intermittent operation class 12, 60 % duty factor) 2 x I _# (with intermittent operation class 12, 25 % duty factor)
Number of contacts in series at DC-21A, 240 V	1
Number of contacts in series at DC-23A, 24 V	1
Number of contacts in series at DC-23A, 48 V	2
Number of contacts in series at DC-23A, 60 V	3
Number of contacts in series at DC-23A, 120 V	3
Number of contacts in series at DC-23A, 240 V	5
Switching capacity (main contacts, general use)	25 A, Rated uninterrupted current max. (UL/CSA)
Switching capacity (auxiliary contacts, general use)	10A, IU, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)	P600 (UL/CSA) A600 (UL/CSA)
Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)	320 A
Voltage per contact pair in series	60 V
Motor rating	
Assigned motor power at 115/120 V, 60 Hz, 1-phase	1.5 HP
Assigned motor power at 200/208 V, 60 Hz, 1-phase	3 HP
Assigned motor power at 200/208 V, 60 Hz, 3-phase	3 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase	3 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase	3 HP
Assigned motor power at 460/480 V, 60 Hz, 3-phase	7.5 HP
Assigned motor power at 575/600 V, 60 Hz, 3-phase	10 HP
Contacts	
Control circuit reliability	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)	0
Number of auxiliary contacts (normally closed contacts)	0
Number of auxiliary contacts (normally open contacts)	0
Actuator	
Actuator color	Red
Actuator type	Door coupling rotary drive
Design verification	
Equipment heat dissipation, current-dependent P _{vid}	0 W
Heat dissipation capacity P _{diss}	0 W
Heat dissipation per pole, current-dependent P _{vid}	1.1 W
Rated operational current for specified heat dissipation (I _n)	32 A
Static heat dissipation, non-current-dependent P _{vs}	0 W
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	UV resistance only in connection with protective shield.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of assemblies	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch disconnecter (EC000216)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Switch disconnecter (ec@ss10.0.1-27-37-14-03 [AKF060013])		
Version as main switch		Yes
Version as maintenance-/service switch		Yes
Version as safety switch		No
Version as emergency stop installation		Yes
Version as reversing switch		No
Number of switches		1
Max. rated operation voltage Ue AC	V	690
Rated operating voltage	V	690 - 690
Rated permanent current Iu	A	32
Rated permanent current at AC-23, 400 V	A	
Rated permanent current at AC-21, 400 V	A	32
Rated operation power at AC-3, 400 V	kW	11
Rated short-time withstand current Icw	kA	0.65
Rated operation power at AC-23, 400 V	kW	15
Switching power at 400 V	kW	15
Conditioned rated short-circuit current Iq	kA	1
Number of poles		1
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		0
Number of auxiliary contacts as change-over contact		0
Motor drive optional		No
Motor drive integrated		No
Voltage release optional		No
Device construction		Built-in device fixed built-in technique
Suitable for floor mounting		No
Suitable for front mounting 4-hole		No
Suitable for front mounting centre		Yes
Suitable for distribution board installation		No
Suitable for intermediate mounting		No
Colour control element		Red
Type of control element		Door coupling rotary drive
Interlockable		Yes
Type of electrical connection of main circuit		Screw connection
Degree of protection (IP), front side		IP65
Degree of protection (NEMA)		12