


CR2

CR Cylindrical-type Lithium Battery (Standard type)

Features & Benefits

- Suitable for Camera, Light, etc. because of super high rate discharge.
- Easy to get high rate discharge because manganese dioxide is used in positive electrode and spiral design is adopted at the polar plate.
- Available in consumer market



Applications

Lights, Security devices (electric door locks, Fire alarms), automotive electric components (eCall), Medical Devices(AEDs), etc.

Nominal voltage	3V	
Nominal capacity	850mAh	
Continuous drain	20mA	
Dimensions*1	Diameter(Max.)	15.6mm
	Height(Max.)	27.0mm
Weight*1	Approx. 11.0g	
Operating temperature*2	-40°C ~ +70°C	

Terminal types


Please see the documents for the terminal and lead wire settings.

- [Line up of tab terminal types\(by shape\)](#)
- [Line up of tab terminal types\(by product number\)](#)

*1 Without tabs.

*2 Please consult Panasonic when anticipating usage in operating temperatures between -40°C and -20°C, or 60°C and 70°C.

Discharge temperature characteristics



Panasonic Energy Co., Ltd.

For more information on how Panasonic can assist you with your battery power solution needs call 877-726-2228, visit www.na.industrial.panasonic.com/products/batteries or e-mail oembatteries@us.panasonic.com.

As of April, 2022. Panasonic offers batteries with tabs or lead wires. This data in this document is for descriptive purposes only and is not intended to make or imply any guarantee or warranty. The contents of this product information are subject to change without notice.

