

SAFETY DATA SHEET



CircuitWorks® Boron Nitride Heat Sink Grease (UFI)

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : CircuitWorks® Boron Nitride Heat Sink Grease (UFI)
Product code : CW7250
Product description : grease
Product type : Solid.
Other means of identification : grease
CW7250
Industrial/Professional use
UFI: 96E8-H0G4-9006-27RX

1.2 Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

1.3 Details of the supplier of the safety data sheet

Manufacturer
Chemtronics
8125 Cobb Center Drive
Kennesaw, GA 30152

Tel. 770-424-4888 or toll free 800-645-5244

Distributor

Importer
ITW Contamination Control BV
Saffierlaan 5
VZ-2132 Hoofddorp
The Netherlands

Email: info@itw-cc.com

Tel: +31 88 1307 400
FAX: +31 88 1307 499
Website: www.Chemtronicseu.com

e-mail address of person responsible for this SDS : Importer/Only Representative
Bay 150
Shannon Industrial Estate
Shannon
County Clare
Ireland
V14 DF82
+353 61 771 500
customerservice.shannon@itwpp.com

National contact

SECTION 1: Identification of the substance/mixture and of the company/undertaking

ITW Contamination Control BV
Saffierlaan 5
VZ-2132 Hoofddorp
The Netherlands

Email: info@itw-cc.com

Tel: +31 88 1307 400
FAX: +31 88 1307 499
Website: www.Chemtronicseu.com

1.4 Emergency telephone number

National advisory body/Poison Centre

Telephone number : EMERGENCY HEALTH INFORMATION:
Austria 01 406 43 43, Belgium +070 245 245, Bulgaria +359 2 9154 233,
Croatia +3851 2348 342, Cyprus 1401, Czech Republic +420224 919 293, Denmark
+45 8212 1212, Estonia 16662, Finland 0800 147 111, France +33 (0) 1 45 42 59
59, Germany +49-30-18412-0, Greece (0300) 2107793777, Hungary
+36-80-201-199, Iceland 543-4071, Ireland 01 809 2566, Italy 0382-24444, Latvia
+371 67042473, Lithuania +370 (85)2362052, Luxembourg +352 8002 5500,
Netherlands +31 88 75 585 61, Norway 22 59 13 00, Poland +48 42 2530 400,
Portugal +351 800 250 250, Romania +40213183606, Slovakia +421 2 5477 4166,
Slovenia 112, Spain +34 91 562 0420, Sweden 112
United Kingdom (England or Wales) 0845 46 47 or Scotland 08454 24 24 24 (UK
only)

Supplier

Telephone number : Chemtronics Product Information: 800-TECH-401 (800-832-4401)
Chemtronics Customer Service: 800-645-5244

Hours of operation : 8:00 AM to 5:00 PM

Information limitations : EMERGENCY HEALTH INFORMATION:
EMERGENCY SPILL INFORMATION:
Transport information

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

The product is not classified as hazardous according to Regulation (EC) 1272/2008 as amended.

Ingredients of unknown toxicity : 95.5 percent of the mixture consists of component(s) of unknown acute oral toxicity
95.5 percent of the mixture consists of component(s) of unknown acute dermal toxicity
95.5 percent of the mixture consists of component(s) of unknown acute inhalation toxicity

Ingredients of unknown ecotoxicity : Contains 95.5% of components with unknown hazards to the aquatic environment

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

Signal word : No signal word.

Hazard statements : No known significant effects or critical hazards.

Precautionary statements

Prevention : Not applicable.

SECTION 2: Hazards identification

Response	: Not applicable.
Storage	: Not applicable.
Disposal	: Not applicable.
Supplemental label elements	: FOR INDUSTRIAL USE ONLY For professional use only.
Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles	: Not applicable.
Special packaging requirements	
Containers to be fitted with child-resistant fastenings	: Not applicable.
Tactile warning of danger	: Not applicable.

2.3 Other hazards

Product meets the criteria for PBT or vPvB according to Regulation (EC) No. 1907/2006, Annex XIII	: This mixture does not contain any substances that are assessed to be a PBT or a vPvB.
Other hazards which do not result in classification	: None known.

SECTION 3: Composition/information on ingredients

3.2 Mixtures : Mixture

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

SECTION 4: First aid measures

4.1 Description of first aid measures

Eye contact	: Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
Inhalation	: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur. In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
Skin contact	: Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
Ingestion	: Wash out mouth with water. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.
Protection of first-aiders	: No action shall be taken involving any personal risk or without suitable training.

4.2 Most important symptoms and effects, both acute and delayed

Over-exposure signs/symptoms

Eye contact	: Adverse symptoms may include the following: irritation redness watering
--------------------	--

SECTION 4: First aid measures

- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
irritation
- Ingestion** : Adverse symptoms may include the following:
Ingestion Seek medical attention.

4.3 Indication of any immediate medical attention and special treatment needed

- Notes to physician** : In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
- Specific treatments** : No specific treatment.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : No specific fire or explosion hazard.
- Hazardous combustion products** : Decomposition products may include the following materials:
nitrogen oxides

5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.
- For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

6.2 Environmental precautions

- : Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

6.3 Methods and material for containment and cleaning up

- Small spill** : Move containers from spill area. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

SECTION 6: Accidental release measures

Large spill : Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

6.4 Reference to other sections : See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

7.1 Precautions for safe handling

Protective measures : Put on appropriate personal protective equipment (see Section 8).
Advice on general occupational hygiene : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

7.3 Specific end use(s)

Recommendations : Not available.
Industrial sector specific solutions : Not available.

SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker exposure or environmental releases.

8.1 Control parameters

Occupational exposure limits

No exposure limit value known.

Biological exposure indices

No exposure indices known.

Recommended monitoring procedures : Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

DNELs/DMELs

No DNELs/DMELs available.

PNECs

SECTION 8: Exposure controls/personal protection

No PNECs available

8.2 Exposure controls

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Individual protection measures

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Eye/face protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

Skin protection

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Body protection : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Other skin protection : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Respiratory protection : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

The conditions of measurement of all properties are at standard temperature and pressure unless otherwise indicated.

9.1 Information on basic physical and chemical properties

Appearance

Physical state	: Solid.
Colour	: White. Off-white. [Light]
Odour	: Not available.
Odour threshold	: Not available.
Melting point/freezing point	: Not available.
Initial boiling point and boiling range	: Not available.
Flammability	: Not available.
Lower and upper explosion limit	: Not applicable.
Flash point	: Not applicable.
Auto-ignition temperature	: Not applicable.
Decomposition temperature	: Not available.
pH	: Not available.

SECTION 9: Physical and chemical properties

Viscosity	: Not applicable.
Solubility in water	: Not available.
Partition coefficient: n-octanol/ water	: Not applicable.
Vapour pressure	: Not available.
Relative density	: Not available.
Density	: 1.5 g/cm ³
Vapour density	: Not applicable.
<u>Particle characteristics</u>	
Median particle size	: Not available.

9.2 Other information

9.2.1 Information with regard to physical hazard classes

Explosive properties	: Not applicable
Oxidising properties	: Not applicable

9.2.2 Other safety characteristics

Miscible with water	Not available.
Evaporation rate	: Not available.

SECTION 10: Stability and reactivity

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: The product is stable.
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: No specific data.
10.5 Incompatible materials	: No specific data.
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity

Conclusion/Summary : Not available.

Acute toxicity estimates

N/A

Irritation/Corrosion

Conclusion/Summary : Not available.

Sensitisation

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary : Not available.

Carcinogenicity

Conclusion/Summary : Not available.

Reproductive toxicity

SECTION 11: Toxicological information

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on likely routes of exposure : Not available.

Potential acute health effects

- Eye contact** : May cause eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : May cause skin irritation.
- Ingestion** : Do not ingest. If swallowed then seek immediate medical assistance.

Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : Adverse symptoms may include the following:
irritation
redness
watering
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
irritation
- Ingestion** : Adverse symptoms may include the following:
Ingestion Seek medical attention.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Short term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Long term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Potential chronic health effects

Not available.

- Conclusion/Summary** : Not available.
- General** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Reproductive toxicity** : No known significant effects or critical hazards.

11.2 Information on other hazards

11.2.1 Endocrine disrupting properties

Not available.

SECTION 11: Toxicological information

11.2.2 Other information

Not available.

SECTION 12: Ecological information

12.1 Toxicity

Conclusion/Summary : Not available.

12.2 Persistence and degradability

Conclusion/Summary : Not available.

12.3 Bioaccumulative potential

Not available.

12.4 Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or a vPvB.

12.6 Endocrine disrupting properties

Not available.

12.7 Other adverse effects

No known significant effects or critical hazards.

SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

13.1 Waste treatment methods

Product

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 2008/98/EC.

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Special precautions : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
14.1 UN number or ID number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name				
14.3 Transport hazard class(es)				
14.4 Packing group	-	-	-	-
14.5 Environmental hazards	No.	No.	No.	No.

14.6 Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

14.7 Maritime transport in bulk according to IMO instruments : Not available.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
[EU Regulation \(EC\) No. 1907/2006 \(REACH\)](#)

[Annex XIV - List of substances subject to authorisation](#)

[Annex XIV](#)

None of the components are listed.

[Substances of very high concern](#)

None of the components are listed.

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles : Not applicable.

Other EU regulations

Industrial emissions (integrated pollution prevention and control) - Air : Not listed

Industrial emissions (integrated pollution prevention and control) - Water : Not listed

[Ozone depleting substances \(1005/2009/EU\)](#)

Not listed.

[Prior Informed Consent \(PIC\) \(649/2012/EU\)](#)

Not listed.

SECTION 15: Regulatory information

Seveso Directive

This product is not controlled under the Seveso Directive.

National regulations

International regulations

Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

Montreal Protocol

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

Rotterdam Convention on Prior Informed Consent (PIC)

Not listed.

UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

Inventory list

Australia	: Not determined.
Canada	: Not determined.
China	: Not determined.
Eurasian Economic Union	: Russian Federation inventory : Not determined.
Japan	: Japan inventory (CSCL) : Not determined. Japan inventory (ISHL) : Not determined.
New Zealand	: Not determined.
Philippines	: Not determined.
Republic of Korea	: Not determined.
Taiwan	: Not determined.
Thailand	: Not determined.
Turkey	: Not determined.
United States	: Not determined.
Viet Nam	: Not determined.

15.2 Chemical safety assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

🔍 Indicates information that has changed from previously issued version.

Abbreviations and acronyms :

- ATE = Acute Toxicity Estimate
- CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
- DMEL = Derived Minimal Effect Level
- DNEL = Derived No Effect Level
- EUH statement = CLP-specific Hazard statement
- N/A = Not available
- PBT = Persistent, Bioaccumulative and Toxic
- PNEC = Predicted No Effect Concentration
- RRN = REACH Registration Number
- SGG = Segregation Group
- vPvB = Very Persistent and Very Bioaccumulative

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

CircuitWorks® Boron Nitride Heat Sink Grease (UFI)

SECTION 16: Other information

Classification	Justification
Not classified.	

Full text of abbreviated H statements

Not applicable.

Full text of classifications [CLP/GHS]

Not applicable.

Date of printing : 1/23/2023

Date of issue/ Date of revision : 1/23/2023

Date of previous issue : 1/23/2023

Version : 31

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.