

20V MAX* XR® Brushless Cordless 1/2 in. Hammer Drill/Driver Kit



- **ACCESS HARD TO REACH WORK AREAS:** Compact 7 in. size is 1/2 in. shorter in length** compared to the DCD796, tool head only.
- **HIGH BIT RETENTION** with 1/2 in. metal ratcheting chuck
- **PRO-LEVEL SPEED, CONTROL, AND PRECISION:** High-speed transmission with variable trigger and 2 speed settings (0-650/0-2,000 rpm)

Product Overview

Complete demanding fastening and drilling projects with this 20V MAX* XR® Brushless 1/2 in. Hammer Drill/Driver. Designed to deliver the durability and performance needed on professional jobsites, this tool quickly drives fasteners into thick material. Experience Power™ with this XR® kit that includes (2) 20V MAX* 2Ah batteries, a charger, and a durable storage bag for convenient portability.

Additional Features

- BRIGHTEN DARK WORK AREAS: Adjustable 3-Position, 3 Mode LED with up to 70 Lumens, including LED spotlight mode which features a 20-minute shutoff function for extended work time in low-light spaces
- DESIGNED TO HELP YOU GET MORE DONE with optimized performance and runtime
- MANAGE AND TRACK TOOLS AT THE JOBSITE: Drill/Driver chip pocket accepts Tool Connect™ chip DCE042 and connects with Tool Connect™ Site Manager app for seamless worksite asset management (DCE042 sold separately)

Includes

- (1) DCD805 20V MAX* XR® Brushless Cordless 1/2 in. Hammer Drill/Driver
- (2) DCB203 20V MAX* 2Ah Batteries
- (1) DCB112 Charger
- (1) Kit Bag
- (1) Belt Hook

Specifications

SKU: DCD805D2

No Load Speed (RPM): 0-650 / 0-2,000 rpm

Product Height: 8 1/7 in

Product Weight: 2.95 lbs