

Standard Thermocouple Connector In-Line Socket IS-R/S-F Type R/S IEC




Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet





Standard in-line Socket (dimensions in mm)

Specifications

General Description	Accepts standard round plug pins, contacts are polarised to prevent incorrect connection.			
Thermocouple Type	R/S IEC			
Connector Type	Socket			
Connector Size	Standard			
Colour	Orange			
Max. Temperature	220°C			
+Positive Contact	Copper			
-Negative Contact	Copper Alloy			
Standards Met	BS EN 50212:1997. RoHS			

Ordering Information

Thermocouple Type	Colour Code	Size	Style	Manufacturers Number	Farnell order Number
R/S	IEC	Standard	Socket	IS-R/S-F	2347066

CONNECTORS - 45 (R-S) Dec-23



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers



ANSI PTFE Insulated Twin Twisted Farnell 2443696 Newark 73AC8304

ANSI PFA Insulated Twin Twisted Farnell 2443711 Newark 73AC8297

Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

Best Sellers



Washer Thermocouple Farnell 8597952 Newark 38K1555



Magnet Thermocouple Farnell 2081298 Newark 88T2877



Thermocouples

Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers





IEC Type K Exposed Junction Farnell 4100748 Newark 15J1022



Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.





IEC Thermocouple PCB Socket Farnell 2347056 **Newark 06X5514**



IEC Thermocouple Plug

Farnell 7086362 **Newark 67C1559**



ANSI Thermocouple Socket

> Farnell 2347121 Newark 06X4819



RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers



Farnell 8598550 Newark 38K0883

PT100 Wire **Wound Detector**

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.

Best Sellers



ANSI Thermocouple Farnell 2420317 Newark 53X3217

IEC Thermocouple with Mini Plug

Farnell 4248338 **Newark 19J1166**

IEC Melt Bolt Thermocouple Farnell 2816490 Newark 44AC8638



Best Sellers



Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974



Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature

Sensor Farnell 2816462 Newark 44AC8648

L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers







L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.