



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Covers



Connector Cover Type: **Dust Cap**

Number of Positions: **68**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Cover Type	Dust Cap
----------------------	----------

Configuration Features

Number of Positions	68
---------------------	----

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: DEC 2012 (138) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5750752-2
68 50SR BKSHLL KIT W/BOOT BULK

Also in the Series | AMPLIMITE 0.50 Series



D-Sub Backshells & Clamps(31)



D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(76)



Insertion & Extraction Tools(1)




PCB D-Sub Connectors(178)

Customers Also Bought



TE Part #2-1986711-3
SCREWLESS, SW,23P,5.0 PCB



TE Part #1-2307729-6
16P,2MM,B-B,REC,DRHZ,SMD,0.1AU,
TR



TE Part #2331370-1
DET SW4.7X3.8X2.3 GW VERT. NO
AG RL



TE Part #2-1617108-3
HS-26B = HS RELAY



TE Part #2031991-1
SDE JPT 12-24AWG ASSY



TE Part #2367197-5
1.0mm WTB Side Vertical Type With
Latch



TE Part #5-1879272-8
RP 2A 374R 0.1% 15PPM CUT LENGTH



TE Part #2176368-2
RQ 0603 51K1 0.1% 10PPM 1K RL



TE Part #1-2176375-3
RQ 0805 1K54 0.1% 10PPM 1K RL

Documents

Product Drawings

[68 DUST COVER,.025 C/L](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_786531-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_786531-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_786531-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



[Application Specification](#)

English

[Instruction Sheets](#)

[Customer Manual \(U.S.\)](#)

English