



Tools for
Advancing
Innovation

Ergonomic
Design

View Through
Eyepieces Or
Monitor

Two Sources
Of Illumination


Top &
Bottom
LED's

10x-44x
continuous
zoom

10x
Eyepieces

Smooth
Motion

Coarse/Fine
Focus
Adjustment



Microscope System
with optional camera



DSZV-44

Trinocular Stereo Zoom Microscope

On Track Stand w/ Top & Bottom LED Illumination

Dual View Trinocular allows you to view images through both eyepieces and through the trinocular port simultaneously. Provides crisp clear 3D images and a wide field of view. 10x to 44x continuous zoom with 10x eyepieces. Microscope is mounted to our track stand with top and bottom LEDs. Focusing Distance: 106mm and length of track: 280mm

Features

- Top and Bottom LED Lights
- Built-in clips for securing slides
- Frosted glass diffusion plate
- Coarse and fine focus adjustment
- Large working distance (280mm track) 90mm with DSZ-44
- 17mm (0.67") high eye point wide field 10x eyepieces (field number 23) for comfortable viewing even for operators with eyeglasses
- C-Mount trinocular port for camera connectivity

DSZV-44 Trinocular Stereo Zoom Microscope On Track Stand With Top And Bottom LEDs

Item Number	DSZV44-506
Magnification	10x-44x
Field Of View	23mm to 5.2mm (0.90"; to 0.20");
Zoom Ratio	4.4:1
LED Wattage	3W each
Base Size	284.7x237.7x45.5mm
Working Distance	90mm
Package Contents	Stereo Zoom Trinocular Microscope Track stand with Top & Bottom LEDs