

## 150mm 370W 230V HEAVY DUTY BENCH GRINDER

### CATALOGUE ENTRY

**57 GHD150**  
**150mm 370W 230V HEAVY DUTY BENCH GRINDER**

A heavy duty model designed for use in the garage or industrial workshop. One coarse and one fine grinding wheel, adjustable eye protection shields, spark deflectors, wheel guards and tools rests. Fitted with a BS approved non-rewireable 3 pin moulded plug and cable. Display carton.

**Specification:**

Grinding wheel diameter	... 150mm
Bore size	... 12.7mm
Speed	... 2850rpm
Machine dimensions	... 360 x 220 x 245mm
Nett/gross weight	... 11/12kg

Stock No.	Euro each	GBP £ each
<b>29620</b>	N/a	N/a

**DRAPER BULLETS**

these need to be kept to a minimum, in order of priority.

- 2850rpm
- Complete with one fine and one coarse grinding wheel



Stock No.	Chk Digit	Description	FARNELL CODE
29620	0	230V 150MM HEAVY DUTY BENCH GRINDER	559430

BRAND:	<b>DRAPER</b>	BARCODED	<b>YES</b>
--------	---------------	----------	------------