




Technical Data Sheet

VA8041

*Environmental Meter
Thickness Gauge*



Product Specifications

Ultrasonic frequency	5MHz
Digital display	4 digits
Measurement Range	1.2mm~225mm (steel)
Pipe measures	minimum dia. 20*3mm (steel)
Velocity Range	1000~9999 m/s
Resolution	0.1mm
Accuracy	± (1%H+0.1mm)
Response time	0.5S
Operating temperature	0~40°C (32~104°F)
Operating humidity	10 to 90%RH



Sifam Tinsley Instrumentation Inc.
2105 Barrett Park Drive, Unit 105
Kennesaw, GA 30144 (USA)
E-mail Id : psk@sifamtinsley.com
Web : www.sifamtinsley.com
Contact No. : +1 678 881 0008 / 800 879 6171