







**Dimensions: [mm]**



**Recommended Land Pattern: [mm]**



**Schematic:**



**Electrical Properties:**

Properties	Test conditions	Value	Unit	Tol.
Inductance	L 100 MHz	1	nH	±0.1nH
Q-Factor	Q 100 MHz	4		min.
DC Resistance	R <sub>DC</sub> @ 20 °C	0.11	Ω	max.
Rated Current	I <sub>r</sub> ΔT = 20 K	470	mA	max.
Self Resonant Frequency	f <sub>res</sub>	10000	MHz	min.

**Certification:**

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACH Approval	Conform or declared [(EC)1907/2006]
Halogen Free	Conform [JEDEC JS709B]
Halogen Free	Conform [IEC 61249-2-21]
Component Qualification	AEC-Q200 Grade 1

**General Information:**

Ambient Temperature (referring to I <sub>p</sub> )	-55 up to +105 °C
Operating Temperature	-55 up to +125 °C
Storage Conditions (in original packaging)	< 40 °C ; < 75 % RH
Moisture Sensitivity Level (MSL)	1




**WURTH ELEKTRONIK**  
MORE THAN YOU EXPECT

Wurth Elektronik eSOS GmbH & Co. KG  
EMC & EMC Solutions  
Max-Eyth-Str. 1  
744838 Waiblingen  
Germany  
Tel. +49 (0) 7142 945-0  
www.we-online.com  
eSos@we-online.com


CHECKED J.Ma	REVISION 002.000	DATE (YY/MM/DD) 2021-11-15	GENERAL TOLERANCE DIN ISO 2768-1m	PROJECTION METHOD 
DESCRIPTION <b>WE-MK SMT Multilayer Ceramic Inductor</b>				
ORDER CODE <b>7447820010G</b>				
SIZE/TYPE 0201	BUSINESS UNIT eSOS	SRIOUS Valid		PAGE 1/6






This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of this product is especially expected by usage, design, assembly, processing, repair or death, unless the notice has been specifically approved for such use. Moreover, Wurth Elektronik eSOS GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network, etc.. Wurth Elektronik eSOS GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Typical Inductance vs. Frequency Characteristics:





Q-Factor vs. Frequency:



   	WURTH ELEKTRONIK <b>MORE THAN YOU EXPECT</b>			Wurth Elektronik eSos GmbH & Co. KG EPC & eSolutions Max-Eyth-Str. 1 744838 Waiblingen Germany Tel. +49 (0) 7142 945-0 www.we-online.com eSos@we-online.com		
	WURTH ELEKTRONIK <b>MORE THAN YOU EXPECT</b>			Wurth Elektronik eSos GmbH & Co. KG EPC & eSolutions Max-Eyth-Str. 1 744838 Waiblingen Germany Tel. +49 (0) 7142 945-0 www.we-online.com eSos@we-online.com		
CHECKED: J.Ma REVISION: 002.000 DATE (YY/MM/DD): 2021-11-15 GENERAL TOLERANCE: DIN ISO 2768-1m PROJECTION METHOD: 		DESCRIPTION: <b>WE-MK SMT Multilayer Ceramic Inductor</b>		ORDER CODE: <b>7447820010G</b>		
SIZE/TYPE: 0201		BUSINESS UNIT: eSos		STATUS: Valid PAGE: 2/6		


This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of this product is especially expected to cause severe personal injury or death, unless the notice has been specifically approved in such case. Wurth Elektronik eSos GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc... Wurth Elektronik eSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

# Packaging Specification - Tape and Reel: [mm]





Packaging is referred to the international standard IEC 60286-2:2015

Tape Type	A0 (mm)	B0 (mm)	W (mm)	T (mm)	T1 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	D0 (mm)	E1 (mm)	E2 (mm)	F (mm)	Material	Qty. (pcs.)
Tolerance	typ.	typ.	+0,3/-0,1	ref.	ref.	±0,1	±0,05	±0,05	±0,1/-0,0	min.	min.	±0,05		
Value	0,38	0,68	8,00	1,10	0,10	4,00	2,00	2,00	1,50	1,75	6,25	3,50	Paper	15000



**Tape width** 8 mm  
**Pull-of force** 0,1 N - 1,0 N



A (mm)	B (mm)	C (mm)	D (mm)	N (mm)	W1 (mm)	W2 (mm)	W3 (mm)	Material
Tolerance	+2,0				+1,5	max.	min.	
Value	1,78	1,5	12,8	20,2	8,4	14,4	7,9	10,9

WURTH ELEKTRONIK  
MORE THAN YOU EXPECT

Wurth Elektronik eSos GmbH & Co. KG  
EMC & EMI Solutions  
Molz-Fabrik-Str. 1  
744838 Wehrburg  
Germany  
Tel. +49 (0) 79 42 945 - 0  
www.we-online.com  
eSos@we-online.com

**WE-MK SMT Multilayer Ceramic Inductor**

ORDER CODE: **7447820010G**

DATE (YY-MM-DD): 2021-11-15  
GENERAL TOLERANCE: DIN ISO 2768-1m


CHECKED: J.Ma  
REVISION: 002.000

SIZE/TYPE: 0201  
BUSINESS UNIT: eSos  
STATUS: Valid

PAGE: 3/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of this product is especially expected by usage, e.g. in aircraft, space, nuclear, nuclear power, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc.. Wurth Elektronik eSos GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear power, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc.. Wurth Elektronik eSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

### Classification Reflow Profile for SMT components:



### Classification Reflow Soldering Profile:

Profile Feature	Value
Preheat Temperature Min	$T_{s \text{ min}}$ 150 °C
Preheat Temperature Max	$T_{s \text{ max}}$ 200 °C
Preheat Time $t_s$ from $T_{s \text{ min}}$ to $T_{s \text{ max}}$	60 - 120 seconds
Ramp-up Rate ( $T_L$ to $T_p$ )	3 °C/second max.
Liquidous Temperature	$T_L$ 217 °C
Time $t_L$ maintained above $T_L$	60 - 150 seconds
Peak package body temperature	$T_p \leq T_c$ , see Table below
Time within 5 °C of actual peak temperature	$t_p$ 20 - 30 seconds
Ramp-down Rate ( $T_p$ to $T_L$ )	6 °C/second max.
Time 25 °C to peak temperature	8 minutes max.

refer to IPC/ JEDEC J-STD-020E

### Package Classification Reflow Temperature ( $T_c$ ):

Properties	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> >2000
PB-Free Assembly   Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly   Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E



Wurth Elektronik eSos GmbH & Co. KG  
 EMC & Electronic Solutions  
 Max-Eyth-Str. 1  
 744838 Waiblingen  
 Germany  
 Tel. +49 (0) 7142 945-0  
 www.we-online.com  
 eSos@we-online.com

CHECKED	REVISION	DATE (YY/MM/DD)	GENERAL TOLERANCE	PROJECTION METHOD
J.Ma	002.000	2021-11-15	DIN ISO 2768-1m	
<b>DESCRIPTION</b>				
<b>WE-MK SMT Multilayer Ceramic Inductor</b>				
ORDER CODE			7447820010G	
SIZE/TYPE	BUSINESS UNIT	PAGE		
0201	eSos	Valid 4/6		

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is especially expected by usage, e.g. in nuclear power plants, in aircraft, in medical, in public information network etc.. Wurth Elektronik eSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

## Cautions and Warnings:

### The following conditions apply to all goods within the product series of WE-MK of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektronik's specifications, for its validity and sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

#### Product specific:

#### Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty. Wave soldering is allowed for components bigger than 0805 after evaluation and approval.
- All other soldering methods are at the customers' own risk.

#### Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.

#### Potting:

- If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the components. We recommend a manual inspection after potting to avoid these effects.

#### Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.








#### Packaging:

- The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

#### Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

    	 <p><b>WÜRTH ELEKTRONIK</b> MORE THAN YOU EXPECT</p>	<p>Würth Elektronik eiSos GmbH &amp; Co. KG EMC &amp; EMI Solutions Max-Eyth-Str. 1 744838 Waiblingen Germany Tel. +49 (0) 71 42 945 - 0 www.we-online.com eiSos@we-online.com</p>	<p>CHECKED J.Ma</p>	<p>REVISION 002.000</p>	<p>DATE (YY-MM-DD) 2021-11-15</p>	<p>GENERAL TOLERANCE DIN ISO 2768-1m</p>	<p>PROJECTION METHOD </p>
<p>DESCRIPTION <b>WE-MK SMT Multilayer Ceramic Inductor</b></p>			<p>ORDER CODE <b>7447820010G</b></p>				
<p>SIZE/TYPE 0201</p>			<p>BUSINESS UNIT eiSos</p>	<p>STATUS Valid</p>	<p>PAGE 5/6</p>		

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is especially expected to cause severe personal injury or death, unless the notice has been specifically preventing such use. Würth Elektronik eiSos GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network, etc.. Würth Elektronik eiSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

