

2 Port Low Profile Native RS232 PCI Express Serial Card with 16550 UART

Product ID: PEX2S553LP



The PEX2S553LP low profile/half-height PCI Express Serial Card turns a PCI Express slot into two RS232 (DB9) serial connections.

The card is constructed using a native single chip design that lets you harness the full capability offered by PCI Express (PCIe), while reducing the load applied to the CPU by as much as 48% over conventional bridge chip serial cards.

The PCI Express RS232 Serial Adapter Card is compatible with a broad range of operating systems, including Windows, and Linux Kernel 2.6.11 to 4.11.x, and ships with a low profile/half-height bracket installed but includes an optional full profile bracket that lets you add 2 serial ports to virtually any computer (regardless of the case form factor).

This product is a replacement for our PEX2S552LP card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility







Applications

• Self service automated machines and kiosks to control serial devices such as scales, touchscreens, magnetic card readers, bar code scanners, receipt printers, label printers

• Bank teller workstations in either full profile or low profile versions to control their serial devices such as cash drawers, card readers / card swipes, printers, keypads / pinpads, pen pads

• POS retail applications in grocery stores, and any other retail store to control keyboards, cash drawers, receipt printers, card readers / card swipes, scales, and elevated displays on poles

• Standard ATM automated teller machines to control keypads, receipt printer, card readers / card swipes, touchscreen LCD's, camera control, etc.

• Used to control multiple surveillance / security cameras in a parking structure, office building, etc.

Features

- One high speed RS232 serial port with data transfer rate up to 460.8 Kbps
- Ships with half-height/low profile mounting bracket, includes optional standard profile bracket
- · Single chip design optimizes speed and reliability
- Native single-chip, single lane PCI Express
- Selectable power output on pin 9 for the serial port
- Compliant with PCI Express base specifications revision 1.1a
- Automated out-of-band flow control using CTS/RTS and DSR/DTR
- Automated in-band software flow control using programmable Xon/Xoff in both directions
- 128-byte deep FIFO per transmitter and receiver

Warranty	2 Years
Ports	1
Interface	Serial
Bus Type	PCI Express
	Ports





	Card Type	Low Profile (SP bracket incl.)
	Port Style	Integrated on Card
	Chipset ID	ASIX - MCS9922CV-AA
Performance		
renormance	Serial Protocol	RS-232
	Max Baud Rate	460.8 Kbps
	FIFO	128 Bytes
Connector(s)		
	Connector Type(s)	1 - PCI Express x1
	Internal Ports	1 - LP4 (4 pin; Large Drive Power)
	External Ports	2 - DB-9 (9 pin, D-Sub)
Software		
	OS Compatibility	Windows DOS, 95, 98SE, 2000, CE 5.0/6.0, Embedded System 2009, POS Ready 2009, XP Embedded, XP, Vista, 7, 8, 8.1, 10, 11
		Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019, 2022
		Mac OS X 10.4 to 10.10
		Linux kernel 2.6.x and up - <i>LTS Versions only</i>
	Microsoft WHQL Certified	Yes
Environmental		
	Operating Temperature	-10C to 80C (14F to 176F)
	Storage Temperature	-20C to 100C (-4F to 212F)
	Humidity	5~85% RH
Physical Characteristics		
	Color	Green
	Material	Steel
	Product Length	4.1 in [10.5 cm]



	Product Width	3.1 in [8 cm]
	Product Height	0.8 in [2 cm]
	Weight of Product	2.2 oz [63.5 g]
Packaging Information		
	Package Quantity	1
	Package Length	6.6 in [16.8 cm]
	Package Width	5.7 in [14.4 cm]
	Package Height	1.2 in [3.0 cm]
	Shipping (Package) Weight	5.4 oz [152.0 g]
What's in the Box		
	Included in Package	1 - PCI-Express Serial Card
		1 - DB9 Ribbon cable
		1 - Full Profile Bracket
		1 - Low profile bracket
		1 - Driver CD
		1 - Instruction Manual

*Product appearance and specifications are subject to change without notice.

