

## VDE 8122-160 H

### VDE Round nose pliers

with insulating sleeves

Code	ETIM
1552104	EC000834
EAN	UNSPSC
4010886816004	27-11-21-25
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



### Article description

- With long jaws, serrated gripping faces
- For gripping and bending
- GEDORE special hardened and tempered steel, drop-forged, oil-hardened and annealed
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900

### Article information

Contents (Qty of pieces)	1	Tip diameter	2,5 mm
Total length [mm]	160 mm	Jaw length L3 [mm]	48 mm
Material	Heat-treated steel	Head thickness [mm] T1	8,7 mm
Handle design	2-component grips VDE insulated up to 1000 V.	Design non-sparking	No
Surface	chrome-plated	Opening spring present	no
Net weight [kg]	0,154 kg	ESD Yes/No	no
Total width [mm]	51 mm	Joint types	inserted joint
Total height [mm]	26 mm	Baking mold	round jaws
Width of head 1 [mm]	16,5 mm	with cutting edge	no
Standard	EN 60900/IEC60900 DIN ISO 5745		