


SEE PDM SCALE: 14:1

SHEET 1 OF 2

RECOMMENDED MECHANICAL PCB FOOTPRINT



MATERIAL: SEE NOTES FINISH: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' DECIMAL: .X ±.030 .XX ±.010	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES [MILIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 151 & LAST THREADS.		WWW.svmicrowave.com	
SURFACE AREA: N/A	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	 4) CHAW: 151 & LAST THREP 5) SURFACE ROUGHNESS 6: 6) DIA: S ON COMMON CENT WITHIN T.I.R. 7) REMOVE ALL BURRS 	3eMIL-STD-10.		ED SMPM MALE PCB JNCH PRE-TINNED SB
THE INFORMATION CONTAINED IN THIS DI		DRAWN:	SEE SHEET 1		SINCH FILE-TININED 3D
IS THE SOLE PROPERTY OF SV MICROWA ANY REPRODUCTION IN PART OR AS A W WITHOUT THE WRITTEN PERMISSION OF		CHECKED:	SEE PDM	SIZE DWG. NO.	3211-40170
SV MICROWAVE, INC IS PROHIBITED.		APPROVED:	SEE PDM	SCALE: 14:1	SHEET 2 OF 2

	REVISION HISTORY						
F	REV	DESCRIPTION	DATE	APPROVED			
		SEE SHEET 1					
				SEE PDM			

