



Tools for  
Advancing  
Innovation

Compact &  
Convenient

Sleek &  
Light-weight  
Design

Two Sources  
Of Illumination



Top &  
Bottom  
LED's

10x-44x  
continuous  
zoom

10x  
Eyepieces

Smooth  
Motion

Coarse/Fine  
Focus  
Adjustment



# DSZ-44

## Binocular Stereo Zoom Microscope

### On Track Stand w/ Top & Bottom LED Illumination

Provides crisp clear 3D images and a wide field of view. 10x to 44x continuous zoom with 10x eyepieces. Microscope is mounted to our track stand with top and bottom LEDs. Base dimensions: 284.7 x 237.7 x 45.5mm

Microscope is mounted to our track stand with top and bottom LEDs. Focusing Distance: 90mm and length of track: 280mm

### Features

- Top and Bottom LED Lights
- Built-in clips for securing slides
- Frosted glass diffusion plate
- Coarse and fine focus adjustment
- Large working distance (280mm track) 90mm with DSZ-44
- 17mm (0.67") high eye point wide field 10x eyepieces (field number 23) for comfortable viewing even for operators with eyeglasses

#### DSZ-44 Binocular Stereo Zoom Microscope On Track Stand With Top And Bottom LEDs

Item Number	DSZ44-506
Magnification	10x-44x
Field Of View	23mm to 5.2mm (0.90"; to 0.20");
Zoom Ratio	4.4:1
LED Wattage	3W each
Base Size	284.7x237.7x45.5mm
Working Distance	90mm
Package Contents	Stereo Zoom Binocular Microscope Track stand with Top & Bottom LEDs