



FPC

TE Internal #: 1-2328702-0

FPC Connectors, Wire-to-Board, 10 Position, .5 mm Centerline,
Non-ZIF, Right Angle, Surface Mount, Height .039 in [1 mm], Gold,
Printed Circuit Board

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors

Connector System: **Wire-to-Board**Number of Positions: **10**Centerline (Pitch): **.5 mm**Insertion Force Type: **Non-ZIF**PCB Mount Orientation: **Right Angle**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Insertion Force Type	Non-ZIF
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	1
Number of Positions	10
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Actuator Color	Black
Primary Product Color	Natural

Contact Features

Contact Layout	Inline
----------------	--------



Contact Shape & Form	Standard Flat
----------------------	---------------

PCB Contact Termination Area Plating Material	Gold
---	------

Contact Base Material	Copper Alloy
-----------------------	--------------

Contact Mating Location	Dual Side
-------------------------	-----------

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Contact Current Rating (Max)	.5 A
------------------------------	------

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Mating Alignment	With
------------------	------

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
------------------	------------------------------

Centerline (Pitch)	.5 mm
--------------------	-------

Dimensions

Connector Length	7 mm
------------------	------

Connector Height	1 mm [.039 in]
------------------	----------------

Accepts Flex Cable Thickness	.3 mm [.01 in]
------------------------------	----------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C [-40 – 185 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC
-----------------	--

Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1734592-0
FPC CONN. 0.5MM PITCH B/C, 10P

Customers Also Bought



TE Part #6-2176230-0
3522 68K 5% 3W




TE Part #5-103634-5
06 MTE HDR SRRA LATCH.100CL LF



TE Part #6318790-1
PLUG ASSY,PB-FREE,2.5 SLIM BATTERY OFF-S



TE Part #2-2328724-5
25PIN 0.3MMP FPC CONNECTOR, FRONT FLIP



TE Part #796683-6
TERMI-BLOK PCB MOUNT 90 6P.



TE Part #2176348-2
CRGCQ 2010 1R5 5%



TE Part #1-208223-0
CPC RCPT ASSEMBLY SIZE 13-9



TE Part #YDTS20F23-55SNV001
RECP ASSY



Documents

Product Drawings

[10PIN 0.5MMP FPC CONN, BACK FLIP LOCK](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-2328702-0_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2328702-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2328702-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773959-6-flexible-printed-circuit-con](#)

English

[1-1773959-7-FPC-Connectors-CN](#)

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English