

har-flex Hybrid M ang 4+16 THR PL1 400pc




Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---------------------------------------------------------------------------------------------|
| Part number | 15 75 416 2701 000 |
| Specification | har-flex Hybrid M ang 4+16 THR PL1 400pc |
| HARTING eCatalogue | https://b2b.harting.com/15754162701000 |

Identification

| | |
|----------------------------|-------------------------------------------|
| Category | Connectors |
| Series | har-flex® |
| Identification | Hybrid |
| Element | Male connector |
| Description of the contact | Angled |
| Features | Termination method of power contacts: THR |

Version

| | |
|---------------------------|----------------------------------------------|
| Termination method | Reflow soldering termination (SMT) |
| Connection type | Motherboard to daughtercard Extender card |
| Number of contacts | 20 |
| Number of signal contacts | 16 |
| Number of power contacts | 4 |
| Pack contents | 400 pieces on reel |

Technical characteristics

| | |
|------------------------------------|---------------------|
| Contact spacing (termination side) | 1.27 mm 2.54 mm |
| Contact spacing (mating side) | 1.27 mm 2.54 mm |
| Rated current | 21.5 A |
| Rated voltage | 50 V AC 120 V DC |



Pushing Performance
 Since 1945

Technical characteristics

| | |
|----------------------------------|----------------------------------------------|
| Rated voltage | acc. to IEC 60664-1 |
| Rated impulse voltage | 1.5 kV |
| Pollution degree | 2 |
| Clearance distance | ≥0.4 mm Signal contacts |
| | ≥0.94 mm Power contacts |
| | ≥0.7 mm Signal to power contacts |
| Creepage distance | ≥0.4 mm PCB: Signal contacts |
| | ≥0.94 mm PCB: Power contacts |
| | ≥0.7 mm PCB: Signal to power contacts |
| | ≥0.4 mm Connector: Signal contacts |
| | ≥1.89 mm Connector: Power contacts |
| | ≥1.99 mm Connector: Signal to power contacts |
| Insulation resistance | >10 ¹⁰ Ω |
| Contact resistance | ≤25 mΩ |
| Limiting temperature | -55 ... +125 °C |
| Performance level | 1 |
| Mating cycles | ≥500 |
| Test voltage U _{r.m.s.} | 0.5 kV Signal |
| | 0.84 kV Signal / Power |
| | 0.84 kV Power / Power |
| Isolation group | IIIa (175 ≤ CTI < 400) |
| Moisture Sensitivity Level (MSL) | 1 acc. to ECA/IPC/JEDEC J-STD-020D |
| Process Sensitivity Level (PSL) | R0 acc. to ECA/IPC/JEDEC J-STD-020D |
| Coplanarity of contacts | 0.12 mm |

Material properties

| | |
|-------------------------------------------|---------------------------------|
| Material (insert) | Liquid crystal polymer (LCP) |
| Colour (insert) | Black |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal over Ni Mating side |
| | Sn over Ni Termination side |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Commercial data

| | |
|--------------------------------|------------------------------------------|
| Packaging size | 1 |
| Country of origin | China |
| European customs tariff number | 85366990 |
| GTIN | 5713140205055 |
| eCl@ss | 27460201 PCB connector (board connector) |