




Cable Assemblies > Automotive Cable Assemblies > Electric, Hybrid & Fuel Cell Cable Assemblies



Cable Assembly Type: **HVA280 Pigtail**

Cable Assembly Configuration: **Single Ended**

Connector Type (End A): **HVA280 Plug**

Operating Voltage: **600 VDC**

Operating Temperature Range: **-40 – 125 °C**

### Features

#### Product Type Features

Cable Assembly Type	HVA280 Pigtail
Connector Type (End A)	HVA280 Plug

#### Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

#### Usage Conditions

Operating Temperature Range	-40 – 125 °C
-----------------------------	--------------

#### Operation/Application

Shielded	Yes
----------	-----

#### Other

Cable Assembly Configuration	Single Ended
Cable Assembly Length	5 m

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts

 <p>TE Part # 1-968853-3 AMP MCP 2.8, CONTACT</p>	 <p>TE Part # 4-2103177-1 PLUG ASSY, KEY A, FA, CPA, HVA280-2PHI XE</p>	 <p>TE Part # 1587826-3 CABLE SEAL, SIZE C, HVA280-2PI</p>	 <p>TE Part # 2103181-3 CABLE SEAL RTNR, SIZE C, HVA280-2PI XE</p>
--	---	---	---

### Documents

**Product Drawings**

[HVA280, 2POS, MCP, 4SQMM, CABLE ASSEMBLY](#)

English

**CAD Files**

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-2379991-3\\_B.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-2379991-3\\_B.3d\\_stp.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2379991-3\\_B.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications

[Product Specification](#)

English

[Product Specification](#)

English