

Han DD Push-In module, male 0,14-1,5mm²




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 012 5001
Specification	Han DD Push-In module, male 0,14-1,5mm ²
HARTING eCatalogue	https://b2b.harting.com/09140125001

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han DD [®] module
Size of the module	Single module

Version

Termination method	Push-In
Gender	Male
Number of contacts	12

Technical characteristics

Conductor cross-section	0.14 ... 1.5 mm ²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
	IEC 61373 Category 2
	IEC 60352-7

Commercial data

Packaging size	2
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)