

GPS Passive Antenna, 1597 MHz to 1607 MHz,  
-3dBic, Linear Polarization Small SMA mount



## LCANGPS1008

### Features

- Low Profile
- MIL-STD-810G
- Linearly Polarized
- SMA Male
- IP67 Rated
- Operating Frequency Range 1559 MHz to 1610 MHz

### Applications

- Military, Law Enforcement, or Private Security
- Hand-held/Portable Devices
- Asset and Fleet Tracking
- Scientific Instrumentation
- Oil, Gas, and Mining Industries
- M2M Applications
- GPS L1, GALLILEO E1, AND GLONASS

### Description

L-Com's Active GNSS Antenna LCANGPS1008 is Linearly polarized and conforms to MIL-STD-810G. The LCANGPS1008 is an active GPS L1 band antenna with -3 dBic Gain. These Mil Spec active GNSS antenna units are ideally suited for use in rugged terrain where low profile, low drag, bullet style antennas are needed.

Our GNSS antenna specialists are ready and available to answer any questions you may have on the LCANGPS1008. This high quality multi-standard SMA male antenna meets GPS L1, GALLILEO E1 and GLONASS G1 requirements by operating in the 1559MHz to 1610MHz frequency range.

The LCANGPS1008 GNSS antenna series from L-Com are designed for portable, hand-held, or mobile devices which receive GNSS signals from satellite constellations to triangulate geolocations for navigation, tracking, surveying, mobile network timing, or munitions targeting. Order your Passive GNSS LCANGPS1008 Antenna from L-Com today. There is no MOQ (minimum order quantity) and the product ships same day from our warehouse.

### Configuration

Design	GPS/GNSS
Band Type	Single
Polarization	Linear, Vertical
Connector Type	SMA Male

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	1,597		1,607	MHz
Output VSWR			2.5:1	
Impedance		50		Ohms
Gain	-3			dBic

### Mechanical Specifications

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[GPS Passive Antenna, 1597 MHz to 1607 MHz, -3dBic, Linear Polarization Small SMA mount LCANGPS1008](#)

GPS Passive Antenna, 1597 MHz to 1607 MHz,  
-3dBic, Linear Polarization Small SMA mount



## LCANGPS1008

Radome Material	Polyetherimide
<b>Size</b>	
Length	1.34 in [34.04 mm]
Weight	0.01 lbs [4.54 g]

### Environmental Specifications

#### Temperature

Operating Range	-40 to +71 deg C
Storage Range	-40 to +85 deg C

#### Environment

Humidity	MIL-STD-810G, Meth 507.5, Proc. II, 95% Relative Humidity
Shock	MIL-STD-810G
Vibration	MIL-STD-810G
Corrosion	MIL-STD-810G, Meth 509.5, 4 x 24 h
Altitude	MIL-STD-810G

#### Environmental Specification Notes:

- Operating Temp MIL-STD-810G, Meth. 501.5 & 502.5, Proc.II. Storage Temp MIL-STD-810G, Meth. 501.5 & 502.5, Proc. I.

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:

GPS Passive Antenna, 1597 MHz to 1607 MHz,  
-3dBic, Linear Polarization Small SMA mount



**LCANGPS1008**

ELECTRICAL PERFORMANCES




Figure 1: VSWR

GPS Passive Antenna, 1597 MHz to 1607 MHz,  
-3dBic, Linear Polarization Small SMA mount



## LCANGPS1008




Figure 2: Radiation pattern on ground plane at 1575 MHz (RHCP)

GPS Passive Antenna, 1597 MHz to 1607 MHz, -3dBic, Linear Polarization Small SMA mount from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

