

156 to 163 MHz, Omni Marine Antenna, 4.5 dBi, UHF Female (SO239) Connector, White, Fiberglass Radome, Vertical Polarization

LCMAROM1003



Features

- Marine grade omni antenna
- Fiberglass strong material
- U-Bolt bracket
- SO239 Female connector
- 156 to 163 MHz, 4.5 dBi
- Yacht, boats and other marine vehicles
- Single pole long antenna
- IP67 rated antenna

Applications

- Port operations
- Boater calling
- Commercial and Non-commercial communications
- International distress, safety and calling (156.80 MHz)
- Coast guard communications
- Marine radios on boats, pontoon, sailboats or yacht
- AIS calling
- Marine operators
- Weather monitoring

Description

The L-com LCMAROM1003 is a single band omni marine antenna that ships on the same day as ordered. Our vertical polarized antenna with 156 to 163 MHz frequency range has a UHF female connector. This antenna with a white radome made of fiberglass has an overall length of 65.35 inch, a width of 1.26 inch, and a weight of 2.2 lbs.

L-com's LCMAROM1003 is a single band antenna operating from 156 to 163 MHz with 4.5 dBi gain. The omni directional antenna has a maximum input VSWR of 1.5:1.

L-com has one of the largest in-stock collections of omni directional antennas with our wide selection of superior quality RF parts, that ship same day. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal single band omni antenna as per your requirement.

Configuration

Design	Marine
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Cable Type	SO239
Connector Type	UHF Female
Number of Ports	1

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	156		163	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		4.5		dBi

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [156 to 163 MHz, Omni Marine Antenna, 4.5 dBi, UHF Female \(SO239\) Connector, White, Fiberglass Radome, Vertical Polarization LCMAROM1003](#)

156 to 163 MHz, Omni Marine Antenna, 4.5 dBi, UHF Female (SO239) Connector, White, Fiberglass Radome, Vertical Polarization

LCMAROM1003



Horizontal (Azimuth) HPBW	Omnidirectional		
Input Power		50	Watts

Mechanical Specifications

Radome Material	Fiberglass
Size	
Length	65.35 in [165.99 cm]
Width	1.26 in [32 mm]
Height	2.5 in [63.5 mm]
Weight	2.2 lbs [997.9 g]

Environmental Specifications

Temperature	
Operating Range	-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

156 to 163 MHz, Omni Marine Antenna, 4.5 dBi, UHF Female (SO239) Connector, White, Fiberglass Radome, Vertical Polarization from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

156 to 163 MHz, Omni Marine Antenna, 4.5 dBi, UHF Female (SO239)
 Connector, White, Fiberglass Radome, Vertical Polarization

L-com CAD Drawing

