

**Customer Part:**

**Description**

- Standard 2.5 x 2.0 oscillator in a ceramic package with a hermetically sealed metal lid.
- Model IQXO-794
- Model Issue number 2

**Frequency Parameters**

- Frequency 32.7680MHz
- Frequency Stability  $\pm 25.00$ ppm
- Operating Temperature Range -20.00 to 70.00°C
- Ageing  $\pm 3$ ppm max per year

**Electrical Parameters**

- Supply Voltage 1.8V  $\pm 5\%$
- Current Draw 10.000mA

**Output Details**

- Output Compatibility HCMOS
- Drive Capability 15pF
- Rise and Fall Time 10.0ns max
- Duty Cycle 40/60%
- Output Voltage High: 90% of VS min  
Output Voltage Low: 10% of VS max
- Start Up Time: 10ms max  
0.9ms typ to 90% of final amplitude (under ideal conditions @ 25°C)

**Output Control**

- Standby Function (pin1):  
No Connection = Output Enabled  
>70% VS = Output Enabled  
<30% VS = Output Disabled  
(when disabled output goes to high impedance state)
- Standby Current: 10µA max, 0.5µA typ @ 25°C

**Noise Parameters**

- Jitter (Period pk-pk):  $\pm 80$ ps typ
- Jitter (Phase 12kHz to 20MHz): 1ps max
- Jitter (Period One Sigma):  $\pm 10$ ps typ

**Environmental Parameters**


- Shock: MIL-STD-202, Method 213. Or comparable.
- Vibration: MIL-STD-883, Method 2007. Or comparable.
- Storage Temperature Range: -55 to 125°C

**Compliance**

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

**Packaging Details**

- Tape & reel in accordance with EIA-481  
Quantities below the standard reel size to be supplied on cut tape.  
Standard Quantity: 3,000 Pieces


**Outline (mm)**

**Sales Office Contact Details:**

UK: +44 (0)1460 270200

USA: +1.760 668 8935

 Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

 Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)



## Crystal Clock Oscillator Specification

Part No. + Packaging: **LFSPXO082225**

---

**Customer Part:**

---

**Sales Office Contact Details:**

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)