

**RoHS
Compliant**





Specification

Waterproof Rate : IP67
IP67 Immersed in 1M water for 30 Minutes

Test Conditions

Current Rating : 3A
 Rated Constant Voltage : 60V DC
 Conduct Resistance : 10mΩ max.
 Hi-POT Test : 500V AC, 0.5mA (1Sec)
 Insulation Resistance : 20MΩ Min. By 500V DC
 Durability : 200 Cycles Min.
 Mating And unmating Force : 30 to 60N
 Corrosion Resistance : Salt Spray Test, 48H
 Rated Temperature : -25°C to +70°C
 Rated Humidity : 95% (40°C)
 Flame Rating : UL94V-0

Diagram



Pin Assignments
Front View

No.	Description	Qty.	Material	Plating & Color
A	Cable	1	FEP, PVC 11C × 0.2mm ²	Black
B	Molding		TPU	
C			PVC	

Part Number Table

Description	Part Number
M11 Sensor Cable, 3A, 11 Pin, Female Connector	MP013719

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.