



Digital output module; 12 digital outputs short-circuit proof 24 V DC/1.7 A each; pulse-switching



**Part no. XN-322-12DO-P17
178788**

| General specifications | |
|--|--|
| Product name | Eaton XN-322 Output module |
| Part no. | XN-322-12DO-P17 |
| EAN | 7640130098220 |
| Product Length/Depth | 104.2 millimetre |
| Product height | 16.8 millimetre |
| Product width | 80.3 millimetre |
| Product weight | 0.057 kilogram |
| Certifications | CE IEC/EN 61000-6-2 IEC/EN 61000-6-4 CULus IEC/EN 61131-2 UL File No.: E135462 |
| Product Tradename | XN-322 |
| Product Type | Output module |
| Product Sub Type | None |
| Catalog Notes | The max. heat dissipation is specified as the maximum power produced inside the device's housing. |
| Features & Functions | |
| Electric connection type | Plug-in connection |
| Features | Fieldbus connection over separate bus coupler possible |
| Functions | Short-circuit protection, outputs available |
| General information | |
| Current consumption | 45 mA (typ.), for +5 V power supply (internal), Power supply - Input None mA (typ.), for +24 V, Power supply - Input |
| Degree of protection | IP20 |
| Mounting method | Rail mounting possible |
| Number of channels | 12, Digital Outputs |
| Overvoltage category | III |
| Pollution degree | 3 |
| Product category | XN-322 digital output module |
| Type | Digital I/O module with twelve 24 V DC / 1.7 A short-circuit proof outputs, featuring undervoltage diagnostics for the three power supply rails. XN300 I/O slice module |
| Used with | XN-312-... XN300 |
| Voltage type | DC |
| Ambient conditions, mechanical | |
| Height of fall (IEC/EN 60068-2-32) - max | 1 m |
| Mounting position | Horizontal |
| Shock resistance | 15 g, Mechanical, Half-sinusoidal shock 11 ms, 18 Impacts |
| Vibration resistance | 5 - 8.4 / 8.4 -150 Hz, 3,5 mm / 1 g |
| Climatic environmental conditions | |
| Air pressure | 795 - 1080 hPa (operation) |
| Ambient operating temperature - min | 0 °C |
| Ambient operating temperature - max | 55 °C |
| Ambient storage temperature - min | -20 °C |
| Ambient storage temperature - max | 85 °C |
| Climatic proofing | Dry heat to IEC 60068-2-2 Damp heat, constant, to IEC 60068-2-3 |
| Environmental conditions | Condensation: prevent with appropriate measures |

| | | |
|---|--|---|
| Relative humidity | | 0 - 95 % (non-condensing) |
| Electro magnetic compatibility | | |
| Air discharge | | 8 kV |
| Burst impulse | | 2 kV, Supply cable 1 kV, Signal cable |
| Contact discharge | | 4 kV |
| Electromagnetic fields | | 10 V/m at 0.08 - 1.0 GHz (according to IEC EN 61000-4-3) 1 V/m at 2 - 2.7 GHz (according to IEC EN 61000-4-3) 3 V/m at 1.4 - 2 GHz (according to IEC EN 61000-4-3) |
| Emitted interference | | 40 dB (at 30 - 230 MHz, Class A, radiated, high frequency) 47 dB (at 230 - 1000 MHz, Class A, radiated, high frequency) |
| Radiated RFI | | 10 V |
| Surge rating | | 0.5/0.5 kV, Supply cable, balanced/unbalanced, EMC 1 kV, Signal cable, unbalanced, EMC |
| Voltage dips | | Voltage dips: 10 ms/Voltage fluctuations: Yes |
| Terminal capacities | | |
| Terminal capacity | | 0.2 - 1.5 mm ² , solid, H07V-U 0.25 - 1.5 mm ² , with ferrules with plastic collar according to DIN 46228-1 (ferrules crimped gas-tight) 24 - 16 AWG 0.2 - 1.5 mm ² , flexible without ferrule, H07V-K 0.25 - 1.5 mm ² , with ferrules without plastic collar according to DIN 46228-1 (ferrules crimped gas-tight) |
| Gauge pin | | A1 (according to IEC/EN 60947-1) |
| Stripping length (main cable) | | 10 mm |
| Insulating material group | | I |
| Electrical rating | | |
| Rated operational current (I _e) | | 3.4 A (supply input) |
| Rated operational voltage | | 160 V (terminations) 24 V (terminal + 3) 24 V (terminal +1) 24 V (terminal + 2) |
| Short-circuit protection | | Yes, Short-circuit rating, Digital outputs |
| Supply voltage at AC, 50 Hz - min | | 0 V AC |
| Supply voltage at AC, 50 Hz - max | | 0 V AC |
| Supply voltage at DC - min | | 18 V DC |
| Supply voltage at DC - max | | 30 V DC |
| Communication | | |
| Connection type | | Push-in spring-cage terminal (plug-in connection), Connection design in TOP direction |
| Protocol | | Other bus systems |
| Input/Output | | |
| Delay time | | < 200 µs, Digital outputs, Delay on signal change and resistive load, from Low to High signal < 200 µs, Digital outputs, Delay on signal change and resistive load, from High to Low signal |
| Input current at signal 1 | | 0 mA |
| Load current | | Not specified by plug manufacturer |
| Load resistance | | > 14.1 Ω |
| Number of inputs (digital) | | 0 |
| Number of outputs (digital) | | 12 |
| Output | | Protective devices must be installed directly at the inductive load in order to prevent interference. 12 Digital Outputs (short-circuit proof, 24 V DC, 1.7 A, pulse-switching) |
| Output current | | < 0.5 mA (low level) 1.7 A |
| Output voltage | | < 24 V DC (High level, digital outputs) 24 V DC (digital outputs) < 1 V DC (Low level, digital outputs) |
| Utilization factor | | 50 % (# I _{Amax} = 10.2A) |
| Safety | | |
| Explosion safety category for dust | | None |
| Explosion safety category for gas | | None |
| Potential isolation | | Power supply, Input: no |

| | | |
|--|--|--|
| | | Between Digital outputs: no |
| Design verification | | |
| Equipment heat dissipation, current-dependent P _{vid} | | 0.383 W |
| Heat dissipation capacity P _{diss} | | 0 W |
| Heat dissipation per pole, current-dependent P _{vid} | | 0 W |
| Rated operational current for specified heat dissipation (I _n) | | 0 A |
| Static heat dissipation, non-current-dependent P _{vs} | | 3.529 W |
| 10.2.2 Corrosion resistance | | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures | | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat | | Meets the product standard's requirements. |
| 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects | | Meets the product standard's requirements. |
| 10.2.4 Resistance to ultra-violet (UV) radiation | | Meets the product standard's requirements. |
| 10.2.5 Lifting | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions | | Meets the product standard's requirements. |
| 10.3 Degree of protection of assemblies | | Meets the product standard's requirements. |
| 10.4 Clearances and creepage distances | | Meets the product standard's requirements. |
| 10.5 Protection against electric shock | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections | | Is the panel builder's responsibility. |
| 10.8 Connections for external conductors | | Is the panel builder's responsibility. |
| 10.9.2 Power-frequency electric strength | | Is the panel builder's responsibility. |
| 10.9.3 Impulse withstand voltage | | Is the panel builder's responsibility. |
| 10.9.4 Testing of enclosures made of insulating material | | Is the panel builder's responsibility. |
| 10.10 Temperature rise | | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating | | Is the panel builder's responsibility. |
| 10.12 Electromagnetic compatibility | | Is the panel builder's responsibility. |
| 10.13 Mechanical function | | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |

Technical data ETIM 9.0

| | | |
|---|----|------------|
| Programmable logic controllers PLC (EG000024) / Fieldbus, decentr. periphery - digital I/O module (EC001599) | | |
| Electric engineering, automation, process control engineering / Control, Process Control System (PCS) / Field bus, decentralized peripheral / Field bus, decentralized peripheral - digital I/O module (ecl@ss13-27-24-26-04 [BAA055019]) | | |
| Supply voltage AC 50 Hz | V | 0 - 0 |
| Supply voltage AC 60 Hz | V | 0 - 0 |
| Supply voltage DC | V | 18 - 30 |
| Voltage type (supply voltage) | | DC |
| Number of digital inputs | | 0 |
| Number of digital outputs | | 12 |
| Digital inputs configurable | | No |
| Digital outputs configurable | | No |
| Input current at signal 1 | mA | 0 |
| Permitted voltage at input | V | 0 - 0 |
| Type of voltage (input voltage) | | DC |
| Type of digital output | | Transistor |
| Output current | A | 1.7 |
| Permitted voltage at output | V | 0 - 30 |
| Type of output voltage | | DC |
| Short-circuit protection, outputs available | | Yes |
| Number of HW-interfaces industrial Ethernet | | 0 |
| Number of interfaces PROFINET | | 0 |
| Number of HW-interfaces RS-232 | | 0 |
| Number of HW-interfaces RS-422 | | 0 |
| Number of HW-interfaces RS-485 | | 0 |

| | | |
|--|----|--------------------|
| Number of HW-interfaces serial TTY | | 0 |
| Number of HW-interfaces parallel | | 0 |
| Number of HW-interfaces wireless | | 0 |
| Number of HW-interfaces USB | | 0 |
| Number of HW-interfaces other | | 1 |
| With optical interface | | No |
| Supporting protocol for EtherCAT | | No |
| Supporting protocol for TCP/IP | | No |
| Supporting protocol for PROFIBUS | | No |
| Supporting protocol for CAN | | No |
| Supporting protocol for INTERBUS | | No |
| Supporting protocol for ASI | | No |
| Supporting protocol for KNX | | No |
| Supporting protocol for Modbus | | No |
| Supporting protocol for Data-Highway | | No |
| Supporting protocol for DeviceNet | | No |
| Supporting protocol for SUCONET | | No |
| Supporting protocol for LON | | No |
| Supporting protocol for PROFINET IO | | No |
| Supporting protocol for PROFINET CBA | | No |
| Supporting protocol for SERCOS | | No |
| Supporting protocol for Foundation Fieldbus | | No |
| Supporting protocol for EtherNet/IP | | No |
| Supporting protocol for AS-Interface Safety at Work | | No |
| Supporting protocol for DeviceNet Safety | | No |
| Supporting protocol for INTERBUS-Safety | | No |
| Supporting protocol for PROFIsafe | | No |
| Supporting protocol for SafetyBUS p | | No |
| Supporting protocol for other bus systems | | Yes |
| Radio standard Bluetooth | | No |
| Radio standard WLAN 802.11 | | No |
| Radio standard GPRS | | No |
| Radio standard GSM | | No |
| Radio standard UMTS | | No |
| IO link master | | No |
| System accessory | | Yes |
| Degree of protection (IP) | | IP20 |
| Type of electric connection | | Plug-in connection |
| Time delay at signal change | ms | 0.1 - 0.2 |
| Fieldbus connection over separate bus coupler possible | | Yes |
| Rail mounting possible | | Yes |
| Wall mounting/direct mounting | | No |
| Front built-in possible | | No |
| Rack-assembly possible | | No |
| Suitable for safety functions | | No |
| SIL according to IEC 61508 | | None |
| Performance level according to EN ISO 13849-1 | | None |
| Appendant operation agent (Ex ia) | | No |
| Appendant operation agent (Ex ib) | | No |
| Explosion safety category for gas | | None |
| Explosion safety category for dust | | None |
| Certified for UL hazardous location class I | | No |
| Certified for UL hazardous location class II | | No |
| Certified for UL hazardous location class III | | No |
| Certified for UL hazardous location division 1 | | No |

| | | |
|--|----|-------|
| Certified for UL hazardous location division 2 | | No |
| Certified for UL hazardous location group A (acetylene) | | No |
| Certified for UL hazardous location group B (hydrogen) | | No |
| Certified for UL hazardous location group C (ethylene) | | No |
| Certified for UL hazardous location group D (propane) | | No |
| Certified for UL hazardous location group E (metal dusts) | | No |
| Certified for UL hazardous location group F (carbonaceous dusts) | | No |
| Certified for UL hazardous location group G (non-conductive dusts) | | No |
| Width | mm | 80.3 |
| Height | mm | 16.8 |
| Depth | mm | 104.2 |