



Power supply module; 4 x 24 V DC / 2 A; short-circuit proof

Part no. **XN-322-4PS-20**  
**178796**

<b>General specifications</b>	
Product name	Eaton XN-322 Accessory Power supply
Part no.	XN-322-4PS-20
EAN	7640130098305
Product Length/Depth	104.2 millimetre
Product height	16.8 millimetre
Product width	80.3 millimetre
Product weight	0.057 kilogram
Certifications	UL File No.: E247993 IEC/EN 61000-6-4 IEC/EN 61000-6-2 UL508 IEC/EN 61131-2 CE
Product Tradename	XN-322
Product Type	Accessory
Product Sub Type	Power supply
Catalog Notes	24 VDC system power supply for generating the XN300 system power, 4 x 24 VDC / 2 A, short-circuit proof 9 outputs in 4 power supply groups, max. total current of 6 A Used to distribute system power to XN300 modules; 9 short-circuit proof outputs (24 VDC / GND) in 4 groups (max. 2 A load per output)
<b>Features &amp; Functions</b>	
Electric connection type	Plug-in connection
Features	Fieldbus connection over separate bus coupler possible
Functions	Distributes supplied power to XN300 system components. Module features 9 short-circuit proof outputs (24 V DC/GND) grouped into four power supply groups (max. 2 A each)
<b>General information</b>	
Degree of protection	IP20
Mounting method	Rail mounting possible
Overvoltage category	III
Pollution degree	3
Type	XN300 power supply module
Used with	XN-312-... XN300
Voltage type	DC
<b>Ambient conditions, mechanical</b>	
Height of fall (IEC/EN 60068-2-32) - max	1 m
Mounting position	Horizontal
Shock resistance	15 g, Mechanical, Half-sinusoidal shock 11 ms, 18 Impacts
Vibration resistance	5 - 8.4 / 8.4 -150 Hz, 3,5 mm / 1 g
<b>Climatic environmental conditions</b>	
Air pressure	795 - 1080 hPa (operation)
Ambient operating temperature - min	0 °C
Ambient operating temperature - max	60 °C
Ambient storage temperature - min	-20 °C
Ambient storage temperature - max	85 °C
Climatic proofing	Dry heat to IEC 60068-2-2 Damp heat, constant, to IEC 60068-2-3
Environmental conditions	Condensation: prevent with appropriate measures
Relative humidity	0 - 95 % (non-condensing)
<b>Electro magnetic compatibility</b>	

Air discharge		8 kV (Air discharge) 4 kV (Contact discharge)
Burst impulse		1 kV, Signal cable 2 kV, Supply cable
Electromagnetic fields		10 V/m at 0.08 - 1.0 GHz (according to IEC EN 61000-4-3) 1 V/m at 2 - 2.7 GHz (according to IEC EN 61000-4-3) 3 V/m at 1.4 - 2 GHz (according to IEC EN 61000-4-3)
Emitted interference		47 dB (at 230 - 1000 MHz, Class A, radiated, high frequency) 40 dB (at 30 - 230 MHz, Class A, radiated, high frequency)
Radiated RFI		10 V
Surge rating		0.5/0.5 kV, Supply cable, balanced/unbalanced, EMC 1 kV, Signal cable, unbalanced, EMC
Voltage dips		Voltage dips: 10 ms/Voltage fluctuations: Yes
<b>Terminal capacities</b>		
Terminal capacity		0.2 - 1.5 mm <sup>2</sup> , flexible without ferrule, H07V-K 0.25 - 1.5 mm <sup>2</sup> , with ferrules with plastic collar according to DIN 46228-1 (ferrules crimped gas-tight) 24 - 16 AWG 0.2 - 1.5 mm <sup>2</sup> , solid, H07V-U 0.25 - 1.5 mm <sup>2</sup> , with ferrules without plastic collar according to DIN 46228-1 (ferrules crimped gas-tight)
Gauge pin		A1 (according to IEC/EN 60947-1)
Insulating material group		I
<b>Electrical rating</b>		
Rated control supply voltage		24 V (X1, X2, X3, X4, X5, 9 x output, Sensor/transmitter supply)
Rated operational current (I <sub>e</sub> ) - max		2 A
Rated operational voltage		24 V (X5) 160 V (terminations)
Supply voltage at AC, 50 Hz - min		0 V AC
Supply voltage at AC, 50 Hz - max		0 V AC
Supply voltage at DC - min		18 V DC
Supply voltage at DC - max		30 V DC
<b>Communication</b>		
Connection type		Push-in spring-cage terminal (plug-in connection), Connection design in TOP direction
<b>Input/Output</b>		
Load current		Not specified by plug manufacturer
<b>Safety</b>		
Explosion safety category for dust		None
Explosion safety category for gas		None
<b>Design verification</b>		
Equipment heat dissipation, current-dependent P <sub>vid</sub>		0 W
Heat dissipation capacity P <sub>diss</sub>		0 W
Heat dissipation per pole, current-dependent P <sub>vid</sub>		0 W
Rated operational current for specified heat dissipation (I <sub>n</sub> )		0 A
Static heat dissipation, non-current-dependent P <sub>vs</sub>		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Meets the product standard's requirements.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 9.0

Programmable logic controllers PLC (EG000024) / Fieldbus, decentr. periphery - power supply/segment module (EC001600)		
Electric engineering, automation, process control engineering / Control, Process Control System (PCS) / Field bus, decentralized peripheral / Field bus, decentralized peripheral - feed and segment module (ecI@ss13-27-24-26-10 [BAA071018])		
Supply voltage AC 50 Hz	V	0 - 0
Supply voltage AC 60 Hz	V	0 - 0
Supply voltage DC	V	18 - 30
Voltage type (supply voltage)		DC
Number of HW-interfaces industrial Ethernet		0
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		0
Number of HW-interfaces RS-422		0
Number of HW-interfaces RS-485		0
Number of HW-interfaces serial TTY		0
Number of HW-interfaces parallel		0
Number of HW-interfaces wireless		0
Number of HW-interfaces USB		0
Number of HW-interfaces other		1
With optical interface		No
Supporting protocol for EtherCAT		No
Supporting protocol for TCP/IP		No
Supporting protocol for PROFIBUS		No
Supporting protocol for CAN		No
Supporting protocol for INTERBUS		No
Supporting protocol for ASI		No
Supporting protocol for KNX		No
Supporting protocol for Modbus		No
Supporting protocol for Data-Highway		No
Supporting protocol for DeviceNet		No
Supporting protocol for SUCONET		No
Supporting protocol for LON		No
Supporting protocol for PROFINET IO		No
Supporting protocol for PROFINET CBA		No
Supporting protocol for SERCOS		No
Supporting protocol for Foundation Fieldbus		No
Supporting protocol for EtherNet/IP		No
Supporting protocol for AS-Interface Safety at Work		No
Supporting protocol for DeviceNet Safety		No
Supporting protocol for INTERBUS-Safety		No
Supporting protocol for PROFIsafe		No
Supporting protocol for SafetyBUS p		No
Supporting protocol for other bus systems		No
Radio standard Bluetooth		No
Radio standard WLAN 802.11		No
Radio standard GPRS		No
Radio standard GSM		No

Radio standard UMTS		No
System accessory		Yes
Degree of protection (IP)		IP20
Type of electric connection		Plug-in connection
With potential separation		No
With power supply module		No
Suitable as segment module		No
Remote module		No
Fieldbus connection over separate bus coupler possible		Yes
Bus diagnosis possible		No
Rail mounting possible		Yes
Wall mounting/direct mounting		No
Front built-in possible		No
Rack-assembly possible		No
Suitable for safety functions		No
SIL according to IEC 61508		None
Performance level according to EN ISO 13849-1		None
Appendant operation agent (Ex ia)		No
Appendant operation agent (Ex ib)		No
Explosion safety category for gas		None
Explosion safety category for dust		None
Certified for UL hazardous location class I		No
Certified for UL hazardous location class II		No
Certified for UL hazardous location class III		No
Certified for UL hazardous location division 1		No
Certified for UL hazardous location division 2		No
Certified for UL hazardous location group A (acetylene)		No
Certified for UL hazardous location group B (hydrogen)		No
Certified for UL hazardous location group C (ethylene)		No
Certified for UL hazardous location group D (propane)		No
Certified for UL hazardous location group E (metal dusts)		No
Certified for UL hazardous location group F (carbonaceous dusts)		No
Certified for UL hazardous location group G (non-conductive dusts)		No
Width	mm	80.3
Height	mm	16.8
Depth	mm	104.2