
PXle-2532B Specifications

2023-08-02



Contents

PXIe-2532B Specifications. 3

PXIe-2532B Specifications

This document lists specifications for the PXIe-2532B. All specifications are subject to change without notice.

PXI-2532B Specifications



Caution The protection provided by the PXIe-2532B can be impaired if it is used in a manner not described in this document.

Definitions

Warranted specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

Characteristics describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- **Typical** specifications describe the performance met by a majority of models.
- **Nominal** specifications describe an attribute that is based on design, conformance testing, or supplemental testing.

Specifications are **Warranted** unless otherwise noted.

Conditions

Specifications are valid at 23 °C unless otherwise noted.

All voltages are specified in DC, AC_{pk}, or a combination unless otherwise specified.

Topology

Topologies	<p>1-wire 4 x 128 matrix</p> <p>1-wire 8 x 64 matrix</p> <p>1-wire 16 x 32 matrix</p> <p>1-wire dual 4 x 64 matrix</p> <p>1-wire dual 8 x 32 matrix</p> <p>1-wire dual 16 x 16 matrix</p> <p>1-wire quad 4 x 32 matrix</p> <p>1-wire sixteen 2 x 16 matrix</p> <p>2-wire 4 x 64 matrix</p> <p>2-wire 8 x 32 matrix</p> <p>2-wire 16 x 16 matrix</p> <p>2-wire dual 4 x 32 matrix</p>
------------	--

Input



Caution

This module is rated for Measurement Category I and intended to carry signal voltages no greater than 100 V. This module can withstand up to 500 V impulse voltage. Do not use this module for connection to signals or for measurements within Categories II, III, or IV. Do not connect to MAINS supply circuits (for example, wall outlets) of 115 or 230 VAC.



Caution When hazardous voltages ($>42.4 V_{pk}/60 VDC$) are present on any relay terminal, safety low-voltage ($<42.4 V_{pk}/60 VDC$) cannot be connected to any other relay terminal.

Maximum switching voltage	
Channel-to-channel	100 V
Channel-to-ground	100 V, CAT I
Maximum current	0.5 A (switching or carry, per channel)
Maximum switching power	10 W (per channel)
DC path resistance	
Initial	$<1 \Omega$, warranted
End-of-life	$\geq 2 \Omega$
Open channel	$>1 \times 10 \Omega$
Thermal EMF	
1-wire	$<50 \mu V$
2-wire	$<20 \mu V$
Bandwidth (-3 dB, 50 Ω termination)	
1-wire row/column	≥ 30 MHz
2-wire row/column	≥ 25 MHz
Channel-to-channel crosstalk (50 Ω termination) Channel-to-channel	
10 kHz	<-85 dB

100 kHz	<-65 dB
1 MHz	<-45 dB
Open channel isolation (50 Ω termination) Open channel	
10 kHz	>84 dB
100 kHz	>64 dB
1 MHz	>44 dB

Dynamic

Simultaneous drive limit	40 relays
Relay operate time	0.25 ms
Release time	0.25 ms
Relay life (no load)	
Mechanical	1 \times 10 cycles, typical
Electrical (resistive, <10 pF load)	
10 V, 100 mA	1 \times 10 cycles, typical
20 V, 500 mA	5 \times 10 cycles, typical
100 V, 10 mA	5 \times 10 cycles, typical

Trigger

Input trigger

Sources	PXI trigger lines <0...7>
Minimum pulse width	150 ns
Output trigger	
Destinations	PXI trigger lines <0...7>
Pulse width	Software-selectable: 1 μ s to 62 μ s

Physical

Relay type	Reed
Relay contact material	Rhodium
I/O connectors	2, 150 pos, Samtec ERM8-EM series
Power requirement	
PXI	
5 V	10 W
3.3 V	2 W
PXI Express	
12 V	15 W
3.3 V	2 W
Dimensions (L \times W \times H)	3U, one slot, PXI/cPCI module, PXI Express compatible 18.5 \times 2.0 \times 13.0 cm (7.3 \times 0.8 \times 5.1 in.)

Weight	454 g (1 lb)
--------	--------------

Environment

Operating temperature	0 °C to 55 °C
Storage temperature	-20 °C to 70 °C
Relative humidity	5% to 85%, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m

Indoor use only.

Shock and Vibration

Operational Shock	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC 60068-2-27. Test profile developed in accordance with MIL-PRF-28800F.)
Random Vibration	
Operating	5 Hz to 500 Hz, 0.3 g _{rms}
Nonoperating	5 Hz to 500 Hz, 2.4 g _{rms} (Tested in accordance with IEC 60068-2-64. Nonoperating test profile exceeds the requirements of MIL-PRF-28800F, Class 3.)

Compliance and Certifications

Safety Compliance Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1



Note For safety certifications, refer to the product label or the [Product Certifications and Declarations](#) section.

Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- EN 55022 (CISPR 22): Class A emissions
- EN 55024 (CISPR 24): Immunity
- AS/NZS CISPR 11: Group 1, Class A emissions
- AS/NZS CISPR 22: Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



Note In the United States (per FCC 47 CFR), Class A equipment is intended for use in commercial, light-industrial, and heavy-industrial locations. In Europe, Canada, Australia, and New Zealand (per CISPR 11), Class A equipment is intended for use only in heavy-industrial locations.



Note Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



Note For EMC declarations, certifications, and additional information, refer to the [Product Certifications and Declarations](#) section.

Product Certifications and Declarations

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit ni.com/product-certifications, search by model number, and click the appropriate link.

Environmental Management


NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the **Engineering a Healthy Planet** web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

EU and UK Customers

- **WEEE**—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

电子信息产品污染控制管理办法（中国 RoHS）

-  **中国 RoHS**— NI 符合中国电子信息产品中限制使用某些有害物质指令(RoHS)。关于 NI 中国 RoHS 合规性信息，请登录 ni.com/environment/rohs_china。(For information about China RoHS compliance, go to ni.com/environment/rohs_china.)