



Part Number : [1552210027](#)


Product Description : Flamar Sensor Cable, WSOR Jacket, Braided Shielding Overall, 5 Circuits, 0.34mm² / 22 AWG, 6.10mm (.240") Diameter, 1000.0m (3280.83') Length, Black

Series Number : 155221

Status : Active

Product Category : Industrial Cable

Engineering Number : BS1-5-1X1000M



Documents & Resources

Specifications

[Product Specification 1552200001-P1E.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Industrial Cable
Series	155221
Description	Flamar Sensor Cable, WSOR Jacket, Braided Shielding Overall, 5 Circuits, 0.34mm ² / 22 AWG, 6.10mm (.240") Diameter, 1000.0m (3280.83') Length, Black
Geographic Area	Global
Product Family	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar,Signal and Control
UPC	889056464093

Agency

UL	E172949
----	---------

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

Physical

Bending Radius - Minimum	> 7.5xOD
Cable Length	1000.0m
Circuits (Loaded)	5
Color - Cable Jacket	Black
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.055/kg
Outer Jacket Diameter	6.10mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL AWM 21215 / CSA

Wire Size (AWG)	22
Wire Size mm ²	0.34

Use with Part(s)

Description	Part Number
Micro-Change (M12) Field Attachable Connectors	<u>120071</u>
Ultra-Lock (M12) Single Keyway Field Attachable Connectors	<u>120085</u>
Nano-Change (M8) Field Attachable Connectors	<u>120091</u>

This document was generated on Mar 06, 2024