

PRODUCT-DETAILS

F202 B-25/0.03

F202 B-25/0.03 Residual Current Circuit Breaker 2P B type 30 mA



General Information

Extended Product Type	F202 B-25/0.03
Product ID	2CSF202568R1250
EAN	8012542341253
Catalog Description	F202 B-25/0.03 Residual Current Circuit Breaker 2P B type 30 mA
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. This product is manufactured according to international IEC standards, for the markets where it is required.

Eco Transparency

Environmental Product Declaration - EPD	9AKK108467A3700
---	-----------------

Technical

Standards	IEC/EN 61008
Type of Residual Current	B type
Rated Voltage (U_r)	230 V
Rated Operational Voltage	230 V
Rated Insulation Voltage (U_i)	440 V
Test Voltage (U_t)	170-253 V AC

Rated Impulse Withstand Voltage (U_{imp})	4 kV
Dielectric Test Voltage	2500 V
Input Voltage Type	AC
Rated Current (I_n)	25 A
Rated Residual Current	30 mA
Rated Residual Breaking Capacity ($I_{\Delta m}$)	1 kA
Rated Conditional Short-Circuit Current (I_{nc})	10 kA
Impulse Current	I (max, 8 / 20 μ s) 3000 A
Maximum Surge Current	3 kA
Rated Frequency (f)	50 ... 60 Hz
Power Loss	1.58 W
Electrical Endurance	10000 cycle
Mechanical Endurance	20000 cycle
Number of Poles	2
Number of Modular Spacings per DIN Rail	2
Operating Characteristic	Instantaneous (APR High Immunity)
Overvoltage Category	III
Tightening Torque	2.8 N·m
Delay Time (T)	10 ms
Accessory Type	Auxiliary contact, Signal contact/auxiliary contact, Shunt trip, Undervoltage release, Overvoltage release, Motor operating device, Auto reclosing unit
Mounting Type	DIN-Rail
Screw Terminal Type	Failsafe Bi-directional Cylinder-lift Terminal
Options Provided	None
Mounting Position	Any
Accessories Available	Yes
Number of Batteries	0
Cable Size	25 mm ²
Connecting Capacity	Busbar 10 mm ² Flexible 1 ... 25 mm ² Stranded 1 ... 25 mm ²
Rated Cross-Section	1 - Solid-Core 1 ... 25 mm ²
Wire Stripping Length	12 mm
Terminal Type	Screw Terminals

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C
Degree of Protection	Housing IPX4 Terminals IP2X
Pollution Degree	3
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Resistance to Vibrations acc. to IEC 60068-2-6	0.1 mm or 1 g - 20 cycles at 5...150..5 Hz
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	9AKK106713A5610
REACH Declaration	9AKK108467A9482

Conflict Minerals
Reporting Template
(CMRT)

9AKK108468A3363

Dimensions

Width in Number of Modular Spacings	2
Product Net Width	35 mm
Product Net Height	85 mm
Product Net Depth / Length	69 mm
Product Net Weight	0.220 kg
Built-In Depth (t ₂)	69 mm

Ordering

Minimum Order Quantity	1 piece
Package Level 1 Units	box 1 piece
Package Level 1 Gross Weight	0.236 kg
Customs Tariff Number	85363030
E-Number (Finland)	3214056
E-Number (Sweden)	2160147
Country of Origin	Italy (IT)

Certificates and Declarations

Declaration of Conformity - CE	9AKK106713A5610
--------------------------------	-----------------

Popular Downloads

Data Sheet, Technical Information	9AKK107991A7569
Instructions and Manuals	9AKK107992A0195

Classifications

ETIM 8	EC000003 - Residual current circuit breaker (RCCB)
ETIM 9	EC000003 - Residual current circuit breaker (RCCB)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363030
eClass	V11.0 : 27142201
Object Classification Code	F

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200912R0001	S2C-H6R Auxiliary Contact	S2C-H6R	2	piece
2CDS200922R0001	S2C-S/H6R Signal / Auxiliary Contact	S2C-S/H6R	2	piece
2CDS200946R0001	S2C-H6-11R Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0003	S2C-H6-02R Auxiliary Contact	S2C-H6-02R	1	piece
2CDS200946R0002	S2C-H6-20R Auxiliary Contact	S2C-H6-20R	1	piece
2CSS200933R0011	F2C-A1 Shunt trip	F2C-A1	1	piece
2CSS200933R0012	F2C-A2 Shunt trip	F2C-A2	1	piece
2CSS200911R0005	S2C-UA 230 AC Undervoltage release	S2C-UA 230 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC Undervoltage release	S2C-UA 24 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC Undervoltage release	S2C-UA 24 AC	1	piece
2CSS200911R0008	S2C-UA 48 DC Undervoltage release	S2C-UA 48 DC	1	piece
2CSS200911R0004	S2C-UA 110 AC Undervoltage release	S2C-UA 110 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC Undervoltage release	S2C-UA 400 AC	1	piece
2CSS200911R0001	S2C-UA 12 DC Undervoltage release	S2C-UA 12 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC Undervoltage release	S2C-UA 230 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC Undervoltage release	S2C-UA 110 DC	1	piece
2CSS200911R0003	S2C-UA 48 AC Undervoltage release	S2C-UA 48 AC	1	piece
2CSS200910R0005	S2C-OVP1 Overvoltage release	S2C-OVP1	1	piece
2CSS200993R0005	S2C-OVP2 Overvoltage release	S2C-OVP2	1	piece
2CSF200997R0013	F2C-CM Motor operating device	F2C-CM	1	piece
2CSF200996R0013	F2C-ARI Auto-reclosing unit	F2C-ARI	1	piece
2CSF200995R0013	F2C-ARI30 Auto-reclosing unit	F2C-ARI30	1	piece
2CSF200992R0005	F2C-ARH Auto-reclosing unit	F2C-ARH	1	piece
2CSF200991R0005	F2C-ARH -T Auto-reclosing unit with autotest	F2C-ARH -T	1	piece

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

