

PRODUCT-DETAILS

F204 A S-63/0.3

F204 A S-63/0.3 Residual Current Circuit Breaker 4P A type 300 mA



General Information

Extended Product Type	F204 A S-63/0.3
Product ID	2CSF204201R3630
EAN	8012542784807
Catalog Description	F204 A S-63/0.3 Residual Current Circuit Breaker 4P A type 300 mA
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Circular Value

Circular Design Principles Recyclability Rate	Design for Closing Resource Loops - Standard EN45555 - 52,5 %
Sustainable Material Content	0 %
End of Life Instructions	9AKK108468A4361

Eco Transparency

Environmental Product Declaration - EPD	9AKK108467A3700
--	-----------------

Technical

Standards	IEC/EN 61008 UL 1053
Type of Residual Current	A type
Rated Voltage (U_r)	230/400 V
Rated Operational Voltage	230 / 400 V AC
Rated Insulation Voltage (U_i)	500 V
Rated Impulse Withstand Voltage (U_{imp})	4 kV
Input Voltage Type	AC
Rated Current (I_n)	63 A
Rated Residual Current	300 mA
Rated Conditional Short-Circuit Current (I_{nc})	10 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs})	1 kA
Maximum Surge Current	5 kA
Leakage Current Type	A
Rated Frequency (f)	50 ... 60 Hz
Power Loss	at Rated Operating Conditions per Pole 4.4 W
Power Supply Connection	Arbitrary
Electrical Endurance	10000 cycle
Number of Poles	4
Operating Characteristic	Selective
Position of Neutral Terminals	Right
Mounting Type	DIN-Rail
Options Provided	None
Accessories Available	Yes
Connecting Capacity	Busbar 10 mm ² Rigid 25 ... 25 mm ² Flexible 25 ... 25 mm ²
Rated Cross-Section	4 - Multi-Wired 0...25 mm ² 1 - Solid-Core 25...25 mm ²

Environmental

Ambient Temperature	-25...55 °C
Ambient Air Temperature	Operation -25...55 °C
Degree of Protection	IP2X
Pollution Degree	2
Resistance to Vibrations acc. to IEC 60068-2-6	0.1 mm or 1 g - 20 cycles at 5...150...5 Hz
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	9AKK106713A5602
REACH Declaration	9AKK108467A9482
Environmental Information	Refer to RoHS
SCIP	18f132b0-8f03-4611-9c59-dba03cc369bf Italy (IT)
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC
Short-Circuit Current Rating (SCCR)	300 mA

Dimensions

Width in Number of Modular Spacings	4
Product Net Width	0.070 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.360 kg
Built-In Depth (t ₂)	69 mm

Ordering

Minimum Order Quantity	1 piece
Package Level 1 Units	box 1 piece
Package Level 1 Gross Weight	0.415 kg
Customs Tariff Number	85363030
E-Number (Finland)	3259504
E-Number (Sweden)	2160151
Country of Origin	Italy (IT)

Certificates and Declarations

Declaration of Conformity - CE	9AKK106713A5602
--------------------------------	-----------------

Popular Downloads

Data Sheet, Technical Information	9AKK107991A8329
Instructions and Manuals	9AKK107991A6127

Classifications

ETIM 8	EC000003 - Residual current circuit breaker (RCCB)
ETIM 9	EC000003 - Residual current circuit breaker (RCCB)
EPLAN Catalog Tree	Electrical engineering / Protection devices / Ground fault current circuit breaker
EPLAN Function Definition	Ground fault current circuit-breaker / Ground fault current circuit breakers, 8 connection points / Ground fault current circuit breaker, four-pole 1_2_3_4_5_6_N_N.
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363030
UNSPSC	39121601

eClass	V11.0 : 27142201
IDEA Granular Category Code (IGCC)	4875 >> Residual current circuit breaker (RCCB)
Object Classification Code	F

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200912R0001	S2C-H6R Auxiliary Contact	S2C-H6R	2	piece
2CDS200922R0001	S2C-S/H6R Signal / Auxiliary Contact	S2C-S/H6R	2	piece
2CDS200946R0001	S2C-H6-11R Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0003	S2C-H6-02R Auxiliary Contact	S2C-H6-02R	1	piece
2CDS200946R0002	S2C-H6-20R Auxiliary Contact	S2C-H6-20R	1	piece
2CSS200933R0011	F2C-A1 Shunt trip	F2C-A1	1	piece
2CSS200933R0012	F2C-A2 Shunt trip	F2C-A2	1	piece
2CSS200911R0005	S2C-UA 230 AC Undervoltage release	S2C-UA 230 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC Undervoltage release	S2C-UA 24 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC Undervoltage release	S2C-UA 24 AC	1	piece
2CSS200911R0008	S2C-UA 48 DC Undervoltage release	S2C-UA 48 DC	1	piece
2CSS200911R0004	S2C-UA 110 AC Undervoltage release	S2C-UA 110 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC Undervoltage release	S2C-UA 400 AC	1	piece
2CSS200911R0001	S2C-UA 12 DC Undervoltage release	S2C-UA 12 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC Undervoltage release	S2C-UA 230 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC Undervoltage release	S2C-UA 110 DC	1	piece
2CSS200911R0003	S2C-UA 48 AC Undervoltage release	S2C-UA 48 AC	1	piece
2CSS200910R0005	S2C-OVP1 Overvoltage release	S2C-OVP1	1	piece
2CSS200993R0005	S2C-OVP2 Overvoltage release	S2C-OVP2	1	piece
2CSF200997R0013	F2C-CM Motor operating device	F2C-CM	1	piece
2CSF200996R0013	F2C-ARI Auto-reclosing unit	F2C-ARI	1	piece

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

