


## MPC0730LR20C

Aliases (UPIA0730LR20C0)

Not for New Design

KEMET, MPC, Power, 0.2 uH, 25%, 3126



Click [here](#) for the 3D model.

### Dimensions

L	8mm MAX
W	6.7mm +/-0.3mm
T	4mm MAX
LL	1.5mm NOM
G	2mm +/-0.3mm

### Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	1000

### General Information

Series	MPC
Style	SMD
Chip Size	3126
Description	Shielded, Surface Mount Inductor
Features	High Speed, Large Current DC/DC Converter
RoHS	Yes
Core	Composite

### Specifications

Inductance	0.2 uH
Inductance Tolerance	25%
Temperature Range	-40/+125°C
Rated Temperature	120°C
Shielded	Yes
Current	17.5 Amps (Isat, 20% Drop In Inductance), 23 Amps (Irms, 40C Rise By Self Heating)
DC Resistance	1.2 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.