

COAXIAL TERMINATION, 75 Ohm, BNC, jack (female)

65_BNC-75-0-31/133_N

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power

**Product configuration**

Interface	Gender	Standard
BNC	jack (female)	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Electrical data

Impedance	75Ω
Operating frequency	0 GHz ... 1 GHz
VSWR	1.1
Return loss	26.4 dB

Electrical Data (power)

Average power	1 W at 25 °C ambient temperature. Linearly derated to 0.6 W at 65 °C ambient temperature.
Peak power	500 W peak power

Interface and material data

Interface	BNC / jack (female)	
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating
Outer conductor	Brass	Tri-metal Plating
Body	Brass	Tri-metal Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Piece parts	Material	Plating

Mechanical data

Weight	0.02 kg
--------	---------

COAXIAL TERMINATION, 75 Ohm, BNC, jack (female)

65_BNC-75-0-31/133_N

Environmental data	
Operation temperature	-30 °C ... 65 °C

Ordering Information Table	
Item number	Item description
85218413	65_BNC-75-0-31/133_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1776 / Date of publication: 13.12.2023 / uncontrolled copy