AC Axial Fan

multicomp PRO

RoHS Compliant




Specification

Rated Voltage Rated Current	: 100V AC to 240V AC 50Hz/60Hz : 0.08 A @ 100V AC 0.045 A @ 240V AC
Rated Power Tolerance Rated Speed Max. Airflow at Zero Static Pressure Max. Static Pressure at Zero Airflow Acoustic Noise Insulation Class Ingress Protection Life Expectancy Direction of Rotation	 : 3.6 W : ±20% on Rated Power and Current : 3100 RPM ±10% in Free Air at Rated Voltage : Nominal 90.1 / MIN. 77.9 CFM Nominal 153 / MIN. 132 m³/h : Nominal 0.31 / MIN. 0.25 inch-H2O Nominal 77 / MIN. 62 Pa : Nominal 40.2 dB(A) / MAX. 44 dB(A) : F : None : 70,000 Hours at 40°C, 15-65% RH. : Counter-Clockwise From Blade Side
Mechanical Bearing System Materials of Frame Materials of Fan Blade Impeller Balance Grade Weight	: Ball Bearing System : Thermoplastic PBT of UL 94V-0 : Thermoplastic PPS of UL 94V-0 : G6.3 Per ISO 1940-1:2003(E) : 265 Grams
Environmental Operating Temperature Range Storage Temperature Range Operating Humidity Range Storage Humidity Range	: -25°C to +70°C : -40°C to +70°C : 5 to 90% RH : 5 to 95% RH
 Protection Automatic Restart Soft Start Over Load Protection Locked Rotor Protection 	

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

multicomp PRO



Air Flow & Static Pressure Curve

NOTE: The airflow and static pressure are measured with specific fixture.


Dimensions

	Torque	Screw Spec.	
Screw Type (Pan Head)	Torque	Size	Standard
Machine Screw	3~4 kgf-cm	M4	JIS B1111-1974

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



multicomp PRO



Item	Functions	Wire Type	Colour
AC Cable	L	UL 3266 #24AWG	Crov
	N	UL 3266 #24AWG	Gray
DC Cable	ISO_GND	UL 1007 #24AWG	Black
	FG	UL 1007 #24AWG	Yellow
	PWM	UL 1007 #24AWG	Blue

Dimensions : Millimetres

Part Number Table

Description	Part Number	
AC Axial Fan, 120mm × 38mm, 100V-240V AC	MP-CF4113MBT-10000-A99	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

