

# DUAL-CHANNEL TEMPERATURE LOGGER



**LogTag**®

**UTRED30-16**


Dual-Channel 30 Day Display Logger




The LogTag® UTRED30-16 Temperature Recorder measures and stores up to a total 32,000 temperature readings, 16,000 readings per channel. The logger supports the ST100 probe and can be used on one or both channels if required.

It features a large easy-to-read display and is designed to show 'at a glance' if temperature excursions have occurred during the current day and up to the previous 29 days. If temperature readings are outside pre-set alarm limits, it is indicated by a large X on the display and, if configured, the audible alarm will sound.


# Accessories




**2x AAA Batteries**  
Not Included



**USB Cable**  
Included



**AC Adapter<sup>^</sup>**  
Included



**UTRED/UTREL30 Wall Mount**  
Not Included



**Glycol Buffer**  
Not Included



**Socket Cover\***  
Included (Optional to use)



**External Probe\*\***  
Not Included. (Required)

Compatible probes below:


<b>ST100J</b>	40mm tip length, ø3.2mm.
<b>ST100K</b>	65mm tip length, ø3.2mm.
<b>ST100L</b>	90mm tip length, ø3.2mm.
<b>ST100S</b>	22mm tip length, ø5mm.
<b>ST100T</b>	105mm tip length, ø5mm.
<b>ST100H</b>	Handled with 105mm tip length, ø5mm.
<b>ST100B</b>	Untipped (bare probe).
<b>STX50</b>	5 Meter extension cable for ST10/ST100 probes.

<sup>^</sup>US and EU adapter only  
\*Optional to insert inside an unused Channel port  
\*\*Hot swappable external sensor probes.

Probes are available with a 1.5m or 3m cable.  
E.g. ST100J-15 for 1.5m or ST100J-30 for 3m cable

# Features

---



Read current temperature and latest Min-Max temperature at a glance.




Two socket external probe with auto channel swap function.



Audible alarm and flashing red LED signals a temperature alarm.



Check and reset Min-Max temperature reading at any time.



Can be powered by 2x AAA batteries (user replaceable) if not external powered.



View alarm status for up to 30 days at a glance.



Second battery backup via a coin cell to ensure no data is lost.



Measure and store up to 16,000 readings for each channel– enough for 67 days at 6 minute logging.



Download data via LogTag Analyzer or as a PDF (no software required).



Inspections can be recorded at the push of a button.

# Applications




Bio Science



Food Science



Cold Room



Blood banks



Bio-Pharma / Bio Technology



Pharmaceutical & Vaccines



Bio Storage & logistics



Life Sciences

# Specifications

<b>Product Model</b>	UTRED30-16.
<b>External Sensor Measurement Range</b>	-40°C to +99°C. (-40°F to 210°F).
<b>Operating Temperature Range</b>	-30°C to +60°C 0 – 99 % RH (non-condensing)
<b>Storage Temperature Range</b>	-10°C to +40°C (32°F to +104°F).
<b>Rated Temperature Reading Resolution</b>	Better than 0.1°C (0.2°F) for -30°C to +60°C (-22°F to +140°F). Better than 0.2°C (0.4°F) for -40°C to -30°C (-40°F to -22°F). Better than 0.5°C (0.9°F) for +60°C to +99°C (+140°F to +210°F). LogTag Analyzer currently displays to one decimal place of °C or °F. The native resolution is what is stored in the LogTag®.
<b>Sensor Reaction Time</b>	Typically less than 2 minutes(T90) in moving air (1m/s) for ST100S type
<b>Rated Temperature Reading Accuracy</b>	Better than ±0.5°C (±0.9°F) for -20°C to +40°C (-4°F to +104°F), typically ±0.3°C (0.6°F). Better than ±0.8°C (±1.4°F) for -40°C to -20°C (-40°F to -4°F), typically ±0.5°C (0.9°F). Better than ±0.8°C (±1.4°F) for +40°C to +70°C (+104°F to +158°F), typically ±0.7°C (1.3°F). Better than ±1.2°C (±2.2°F) for +70°C to +99°C (+158°F to +210°F), typically ±1°C (1.8°F).
<b>Probe Connectivity</b>	Up to 2
<b>Probe Compatibility</b>	All ST100 precision thermistor external probes can be interchangeably connected to the UTRED30-16. Please refer to the Accessories section for compatible External Probes. Different probe models can be used for each channel. Not compatible with ST10 sensors.
<b>Recording Capacity</b>	32,000 total log memory. Provides 16,000 temperature readings per channel. Day summary statistics memory (for display on LCD): up to 30 days of Min/Max/duration and alarm trigger statistics.
<b>Sampling Interval</b>	Configurable from 30 seconds to 18 hours. (Typically 5 minute logging)
<b>Alarms</b>	Up to 6 individually configurable alarms for each channel. Possible to set alarms separately for Channel 1 and Channel 2.
<b>Logging Start Options</b>	Push button start or specific date & time. Optional start delay.
<b>Download Time</b>	Typically with full memory (32,000 readings) in less than 20 seconds.
<b>Environmental</b>	IP61 (when vertically mounted or hung with USB dust-cap in place).
<b>Power Source</b>	5V via micro USB socket or 2 x 1.5V AAA batteries. CR2032 LiMnO <sub>2</sub> coin cell (backup logging function only).
<b>Battery Life</b>	AAA battery up to 12 months - if unit is operated without power supply.
<b>Real Time Clock</b>	Built-in real time clock. Typical accuracy ±25ppm @ 25°C (equivalent to 2.5 seconds/day). Rated temperature coefficient is -0.034 ±0.006ppm/°C (i.e typically +/- 0.00294 seconds/day/°C).
<b>Standard Remote Probe Cable Lengths</b>	Standard: 1.5m (4'11"). Extended: 3m (9'10") (recommended maximum).
<b>Remote Probe Cable Type</b>	PTFE (FDA food contact rated) coaxial.
<b>Connection Interface</b>	USB 2.0 / Micro USB Socket.
<b>Size</b>	141mm(H) x 72mm(W) x 18mm(T).
<b>Weight</b>	156g with AAA batteries, (132g – excluding probe and AAA batteries).
<b>Case Material</b>	Polycarbonate.

