# C9T, 415 - 440 VAC, 3-Phase PFC



#### **Overview**

The C9T capacitor is a polypropylene metallized film capacitor with a cylindrical, aluminium can-type design filled with resin. It uses a 3-phase delta connection and safety device FPU.

## **Applications**

Typical applications power factor correction.

#### **Benefits**

- · VDE Approved
- · Overpressure safety device
- · High capacitance density
- · Long lifetime
- · 3-phase delta connections




## **Part Number System**

C9T	S	5	M	D	6137	AAR	X
Series	Туре	Rated Voltage (VAC)	Terminal Style	Internal Connection	Capacitance Code (pF)	Internal Code	Tolerance
C9T = Cylindrical Three-Phase Capacitors	S = Slim	5 = 415 6 = 440	M = Screw clamp Terminal	D = Delta	Digits 2 – 4 indicate the first three digits of the capacitance value*. First digit indicates the number of zeros to be added.	AAR = Standard	X = -5%/+10%

<sup>\*</sup> Capacitance Code (8th - 11th digit) -> Single Capacitive Element Value



### **Dimensions - Millimeters**



D	Н	<b>Mounting Stud</b>	
±0.5	±2	(M)	
75	160	M12 x 16	
75	230	M12 x 16	
75	280	M12 x 16	
85	160	M12 x 16	
85	230	M12 x 16	
85	280	M12 x 16	

# **Qualifications**

Reference Standards	IEC 831-1/2		
Reference Standards	Approved VDE-REG.Nr.F064		
Protected 10,000 AFC	-25°C to +70°C		

## **General Technical Data**

	IEC 60831-1/2			
Reference Standards	Approved VDE-REG.Nr.F064			
	UL810 compliant			
Distriction	Polypropylene film			
Dielectric	Non-Inductive type winding			
	-25/D - IEC 60831-1			
Climatia Catagory	Maximum: 55°C			
Climatic Category	Highest mean over any period of 24 hours: 45°C			
	Highest mean over any period of one year: 35°C			
Maximum Hot Spot Temperature	+70°C			
Endurance Test IEC 60831-2	IEC 60831-2 clause 17.1-17.2			



#### **Electrical Characteristics**

Rated Voltage	Un = (see table) Vrms
Over Voltage	IEC 60831-1 clause 20:
	1,10*UN – 8 hours in every 24 hours
	1,15* UN – 30 minutes in every 24 hours
	1,20* UN – 5 minutes in the lifetime
	1,30* UN – 1 minutes in the lifetime
Capacitance Tolerance	-5% +10% (X)

### **Mechanical Characteristics**

Mayimum Targua	6 [N*m] for Terminal screw			
Maximum Torque:	12 [N*m] for M12 Bolt			
Installation	Whatever position			
Aluminum deck with self extinguishing UL94 V0 plastic cover				

## **Life Expectancy**

Life Expectancy	100,000 hours at $U_{rms}$ with $T_{hs} \le 70^{\circ}$ C
Capacitance drop at end of life	-5% (typical)
Failure rate IEC 61709	300*10-9 components/hours

#### **Test Method**

Test voltage term to term (Utt)	2,15*U <sub>rms</sub> for 2 seconds at 25°C
Test voltage term to case (Utc)	3600 V - 50 Hz for 2 seconds
	Annual average ≤ 80% at 24°C
Relative Humidity	On 30 days/year permanently 100%. On other days occasionally 90%.
	Dewing not admitted
Capacitance Deviation in Temperature Range (-40+50°C)	±1.5% maximum on capacitance value at 20°C
Damp Heat	IEC 60068-2-78
Change of Temperature	IEC 60068-2-14
Vibration Strength	IEC 60068-2-6

**NOTICE:** Care should be taken to ensure that there still is electrical clearance of 15 mm between terminations and other live or earthed parts above the capacitor, in case of safety device activation.




### **Table 1 - Ratings & Part Number Reference**

Capacitance Value	Voltage	Dimensions (mm)		Rated Current	Qn	Operating Frequency	dV/dt	Packaging Quantity	Part Number
μF	VAC	Ø	Н	Α	kVAr	Hz	V/µs		
3 x 31.1	415	75	160	9	5.0	50	30	12	C9TS5MD5311AARX
3 x 46.0	415	75	160	14	7.5	50	30	12	C9TS5MD5460AARX
3 x 61.5	415	85	160	18	10.0	50	30	9	C9TS5MD5615AARX
3 x 77.0	415	75	230	23	12.5	50	30	12	C9TS5MD5770AARX
3 x 92.2	415	85	230	27	15.0	50	30	9	C9TS5MD5920AARX
3 x 108.0	415	75	280	32	17.5	50	30	12	C9TS5MD6108AARX
3 x 123.0	415	75	280	36	20.0	50	30	12	C9TS5MD6123AARX
3 x 154.0	415	85	280	45	25.0	50	30	9	C9TS5MD6154AARX
3 x 27.4	440	75	160	9	5.0	50	30	12	C9TS6MD5274AARX
3 x 41.1	440	75	160	13	7.5	50	30	12	C9TS6MD5411AARX
3 x 54.8	440	85	160	17	10.0	50	30	9	C9TS6MD5548AARX
3 x 68.5	440	75	230	21	12.5	50	30	12	C9TS6MD5685AARX
3 x 83.0	440	85	230	26	15.0	50	30	9	C9TS6MD5830AARX
3 x 96.0	440	75	280	30	17.5	50	30	12	C9TS6MD5960AARX
3 x 110.0	440	75	280	34	20.0	50	30	12	C9TS6MD6110AARX
3 x 137.0	440	85	280	43	25.0	50	30	9	C9TS6MD6137AARX

<sup>(\*)</sup> Maximum admissible RMS current. Ths ≤ 70°C.

### **Marking**





#### **Environmental Compliance**

As a leading global supplier of electronic components and an environmentally conscious company, KEMET continually aspires to improve the environmental effects of our manufacturing processes and our finished electronic components.

In Europe (RoHS Directive) and in some other geographical areas such as China (China RoHS), legislation has been enacted to prevent or otherwise limit the use of certain hazardous materials, including lead (Pb), in electronic equipment. KEMET monitors legislation globally to ensure compliance and endeavors to adjust our manufacturing processes and/or electronic components as may be required by applicable law.

For military, medical, automotive, and some commercial applications, the use of lead (Pb) in the termination is necessary and/or required by design. KEMET is committed to communicating RoHS compliance to our customers. Information related to RoHS compliance will be provided in data sheets and using specific identifiers on the packaging labels.

All KEMET power film capacitors are RoHS compliant.

#### **Materials & Environment**

The selection of raw materials that KEMET uses for the production of its electronic components is the result of extensive experience. KEMET directs specific attention toward environmental protection. KEMET selects its suppliers according to ISO 9001 standards and performs statistical analyses on raw materials before acceptance for use in manufacturing our electronic components. All materials are, to the best of KEMET's knowledge, non-toxic and free from cadmium; mercury; chrome and compounds; polychlorine triphenyl (PCB); bromide and chlorinedioxins bromurate clorurate; CFC and HCFC; and asbestos.

### **Dissipation Factor**

Dissipation factor is a complex function involved with capacitor inefficiency. The  $tg\delta$  may vary up and down with increased temperature. For more information, refer to Performance Characteristics.

## **Sealing**

#### **Hermetically Sealed Capacitors**

As the temperature increases, the pressure inside the capacitor increases. If the internal pressure is high enough, it can cause a breach in the capacitor. Such a breach can result in leakage, impregnation, filling fluid, or moisture susceptibility.

#### **Barometric Pressure**

The altitude at which hermetically sealed capacitors are operated controls the capacitor's voltage rating. As the barometric pressure decreases, the susceptibility to terminal arc-over increases. Non-hermetic capacitors can be affected by internal stresses due to pressure changes. These effects can be in the form of capacitance changes, dielectric arc-over, and/or low insulation resistance. Altitude can also affect heat transfer. Heat that is generated in an operation cannot be dissipated properly, and high RI<sup>2</sup> losses and eventual failure can result.



### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### **Disclaimer**

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.