

Product information

90 59 280 02

Opening spring

For 90 55 280

- For cutting iron, copper or aluminium sheet metal up to max. 1.2 mm thickness, plastic up to max. 2.0 mm thickness
- Materials are cut without deformation
- Clean cut edges - no trimming activities needed
- With chip breaker
- Easy handling
- Cutting width: 2.7 mm
- Tool body: special tool steel, rolled, oil-hardened
- Blades: special tool steel, oil-hardened, interchangeable



General

Article No.	90 59 280 02
EAN	4003773053712
Weight	8 g
Dimensions	75 x 2 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted