



Sliver for SFF-TA-1002

TE Internal #: 2332139-1

Internal I/O Connectors, Sliver for SFF-TA-1002, Cable Plug Assembly, Vertical, Cable-to-Board, Gen-Z, 140 Position, Sliver for SFF-TA-1002

[View on TE.com >](#)

Connectors > PCB Connectors > Internal I/O Connectors



Internal I/O Connector Type: **Sliver for SFF-TA-1002**

Connector Mates With: **Cable Plug Assembly**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Industry Standard: **Gen-Z**

**Features**

**Product Type Features**

Internal I/O Connector Type	Sliver for SFF-TA-1002
Connector Mates With	Cable Plug Assembly
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

Number of Rows	2
PCB Mount Orientation	Vertical
Number of Positions	140

**Contact Features**

Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1.1 A



Contact Mating Area Plating Material Thickness	.076 $\mu\text{m}$ [3 $\mu\text{in}$ ]
--	--

### Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

### Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

### Housing Features

Centerline (Pitch)	.6 mm[.023 in]
--------------------	----------------

### Usage Conditions

Operating Temperature Range	-55 – 85 $^{\circ}\text{C}$ [-67 – 185 $^{\circ}\text{F}$ ]
-----------------------------	---

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

Industry Standard	Gen-Z
-------------------	-------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 2340880-1  
C/A, SLIVER 2.0, 4C, STR TO R/A, 0.5M



TE Part # 2340880-2  
C/A, SLIVER 2.0, 4C, STR TO R/A, 1.0M



TE Part # 2340881-1  
C/A, SLIVER 2.0, 4C, R/A TO R/A, 0.5M



TE Part # 2340881-2  
C/A, SLIVER 2.0, 4C, R/A TO R/A, 1.0M



TE Part # 2340884-1  
C/A, SLIVER 2.0, 4C, STR TO R/A, 0.5M



TE Part # 2340884-2  
C/A, SLIVER 2.0, 4C, STR TO R/A, 1.0M



TE Part # 2340885-1  
C/A, SLIVER 2.0, 4C, R/A TO R/A, 0.5M



TE Part # 2340885-2  
C/A, SLIVER 2.0, 4C, R/A TO R/A, 1.0M



TE Part # 2343288-1  
C/A SLIVER 2.0 4C LTL TO LTL 33AWG 0.5M



TE Part # 2343288-2  
C/A SLIVER 2.0 4C LTL TO LTL 33AWG 1.0M



TE Part # 2349842-1  
C/A, SLIVER 2.0, 4C, STR TO R/A, 0.5M



TE Part # 2349842-2  
C/A, SLIVER 2.0, 4C, STR TO R/A, 1M



TE Part # 2349843-1  
C/A, SLIVER 2.0, 4C, R/A TO R/A, 0.5M



TE Part # 2349843-2  
C/A, SLIVER 2.0, 4C, R/A TO R/A, 1M



TE Part # 2349844-1  
C/A SLIVER 2.0 4C LTL TO LTL 33AWG 0.5M



TE Part # 2349844-2  
C/A SLIVER 2.0 4C LTL TO LTL 33AWG 1M




TE Part # 2361354-1  
C/A, Sliver 2.0 4C, STR to RA, 0.5M



TE Part # 2361354-2  
C/A, Sliver 2.0 4C, STR to RA, 1M




TE Part # 2361355-1  
C/A, Sliver 2.0 4C, STR to RA, 0.5M




TE Part # 2361355-2  
C/A, Sliver 2.0 4C, STR to RA, 1M

## Also in the Series | Sliver for SFF-TA-1002



Card Guide Hardware(1)



Internal I/O Cable Assemblies(109)



Internal I/O Connectors(135)

## Customers Also Bought



TE Part #5745781-4  
09 MSFL RCPT RA 318 (IN,FM)



TE Part #3-647168-3  
03P MTA100 HDR ASSY SM 30AU LF



TE Part #1551892-1  
Cage Assy Behind Bezel QSFP28



TE Part #1-292303-6  
Std USB Type A, R/A, SMT, Offset




TE Part #1551920-2  
zQSFP+ connector assembly



TE Part #2-2176092-4  
RP 2A 0.25W 1K18 0.1% 25PPM 1K RL



TE Part #3-2176370-6  
RQ 0603 1K0 0.1% 10PPM 5K RL



TE Part #1888811-1  
Std HDMI, RA, T/H, Stacked 2x, Panel grd



TE Part #5767044-1  
MICTOR,R/A,RECPT,.062,038,ASY



## Documents

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2332139-1\\_4.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2332139-1\\_4.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2332139-1\\_4.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Sliver Internal Cabled Interconnect Solutions Brochure \(Chinese\)](#)

### Product Specifications

[Application Specification](#)

English