

TECHNICAL DATA

SMFT-1000 Multifunction PV Tester and Performance Analyzer, I-V Curve Tracer



All-in-one test solution to verify PV system performance and safety, expedite client reporting.

Test that PV systems are performing to their optimal power output as well as operating safely with the Fluke SMFT-1000 multifunction tester with I-V curve tracing. Designed for PV professionals that provide installation, commissioning and maintenance services to systems that operate at 1000 V DC or under, the SMFT-1000 provides a complete PV testing solution that conforms to IEC 62446-1 standards. Through Fluke's TruTest™ Software, measurement data from solar site installation and commissioning testing can be easily imported, organized and analyzed for effortless reporting without having to bring a laptop on-site.

**Wireless Irradiance Meter
No leads required**

To perform precise I-V curve measurements, real time irradiance and temperature data is needed. The included IRR2-BT irradiance meter wirelessly connects to the SMFT-1000 to communicate data in real time, providing the most accurate I-V curve measurements possible. If the wireless connection is interrupted for any reason, the IRR2-BT will continue recording data for up to 17 hours that can later be matched to tests taken with the SMFT-1000.

CRITICAL TESTING FEATURES FOR PERIODIC INSPECTION OF PV SYSTEMS

**Full sequence safety testing
–IEC 62446-1 Category 1:**

- Protective resistance earth RLO
- Voltage on open circuit, including polarity VOC
- Short circuit current ISC
- Insulation resistance RINS

**System performance testing
–IEC 62446-1 Category 2:**

- I-V Curve tracing and software analysis with TruTest
- Irradiance, temperature, tilt, cardinal direction



Keep the Leads

Quick and accurate testing saves time and money

It's a hassle to change the configuration of test leads constantly while doing different tests. With Fluke's patented "Keep the Leads" system, less time is wasted on set-up, and less user errors occur while testing PV systems. Now you can get more testing done in the field in less time.



Color Screen with Integrated Interface

On-screen instructions provide any easy walkthrough of tests

Automatic testing saves time

Switch the SMFT-1000 to Auto Test Mode to perform an automatic sequence of tests in a variety of combinations:

- With insulation test or without insulation test
- IEC 62446-1 testing for Category 1 or Category 1 and 2
- IEC 62446-1 testing for Protection Class I or Protection Class II

On-location I-V curve results: compare manufacturer I-V curve data to measured data instantly

While taking an I-V curve reading in the field, the SMFT-1000 will display the curve as it loads in the test data, against the module specifications as defined by the manufacturer. This makes it easy to immediately confirm measurements without the use of a laptop or tablet. Run the I-V curve test on new installations to confirm they are working according to the site specifications, or to test if existing modules or strings are working to their expected performance levels.



Visual Inspection

To meet PV system IEC regulations for visual inspections, the SMFT-1000 features a convenient setting in which to record observations directly to the memory. Later, the information can be downloaded to the TruTest™ software and incorporated into the project report.



TruTest™ Solar Data Management Software

Spend less time processing test results and compiling reports

The reporting necessary to close out projects can be challenging and time-consuming. Cover all your certification and documentation needs through the modern, fast and reliable software platform of TruTest™. TruTest™ allows for solar asset management, data storage and reporting on a single platform. Whether you are analyzing panel efficiency through I-V curves, or safety testing the system through the Category 1 test regime in conformance to IEC 62446-1, proper data management is critical for producing easy-to-understand reports for clients. Compatible with the Fluke SMFT-1000 Multifunction PV Tester and Performance Analyzer, TruTest™ Software allows you to quickly and easily import measurement results directly from your solar multifunction tester to computer, organize and analyze the data, compare individual asset data against previous measurements imported and provide a comprehensive and visual client report.

- Easily manage measurement data from solar site installation and commissioning testing
- Quickly create inspections and reports compliant with IEC 62446-1 and other directives
- I-V curve analysis with easy pass/fail visuals; see changes in I-V curve over multiple site visits
- Easily manage measurement data from solar site installation and commissioning testing
- Compare site data to previous site data to see changes over time



TruTest™

Function	Demo	Lite	Advanced
Maximum addable clients	1	10	Unlimited
Maximum addable site/client	2	5	Unlimited
Maximum addable strings	5	50	Unlimited
Maximum addable modules (per string)	50	50	Unlimited
Edit distribution board information		•	•
Edit circuit information		•	•
Edit inverter information		•	•
Edit combiner box information		•	•
Edit string information		•	•
Edit module information		•	•



Record Data



Export Data



Report Data

Specifications

Protective conductor resistance RLO			
Display range	Measuring range	Resolution	Accuracy
0.00 Ω - 19.99 Ω	0.20 Ω - 19.99 Ω	0.01 Ω	± (2 % + 2 Digit)
20.0 Ω - 199.9 Ω	20.0 Ω - 199.9 Ω	0.1 Ω	± (2 % + 2 Digit)
200 Ω - 2000 Ω	200 Ω - 2000 Ω	1 Ω	± (5 % + 2 Digit)
Test current	≥ 200 mA (≤ 2Ω + Rcomp)		
Test voltage	4 V DC ... 10 V DC		
Polarity reversing	Yes		
Test lead zero (Rcomp)	Up to 3 Ω		
PV module/PV string, open-circuit voltage (Voc)			
Display range	Measuring range	Resolution	Accuracy
0.0 V - 99.9 V	5.0 V - 99.9 V	0.1 V	± (0.5 % + 2 Digit)
100 V - 1000 V	100 V - 1000 V	1 V	± (0.5 % + 2 Digit)
Polarity test	Yes		
PV module/PV string, short-circuit current (Is/c)			
Display range	Measuring range	Resolution	Accuracy
0.0 A - 20.0 A	0.2 A - 20.0 A	0.1 A	± (1 % + 2 Digit)

Insulation resistance RINS

Display range	Measuring range	Resolution	Accuracy
0.00 MΩ - 99.99 MΩ	0.20 MΩ - 99.99 MΩ	0.01 MΩ	± (5 % + 5 Digit)
100.0 MΩ - 199.9 MΩ	100.0 MΩ - 199.9 MΩ	0.1 MΩ	± (10 % + 5 Digit)
200 MΩ - 999 MΩ	200 MΩ - 999 MΩ	1 MΩ	± (20 % + 5 Digit)
Test voltage @ no load	50 V / 100 V / 250 V up to 199.9 MΩ 500 V / 1000 V up to 999 MΩ	1 V	0 % to + 20 %
Test voltage @ ≥ 1 mA	250 V @ 250 kΩ 500 V @ 500 kΩ 1000 V @ 1 MΩ	1 V	0 % to + 10 %
Testing current	Min. 1 mA (@ 250 kΩ / 500 kΩ / 1 MΩ) Max. 1.5 mA (short circuit)		

Overvoltage protective devices (BV)

Display range	Measuring range	Resolution	Accuracy
0 V DC - 1000 V DC	50 V DC - 1000 V DC	1 V DC	± (10 % + 5 Digit)

AC/DC voltage measurement via 4 mm test sockets

Display range	Measuring range	Resolution	Accuracy
0.0 V AC - 99.9 V AC	5.0 V AC - 99.9 V AC	0.1 V	± (2.5 % + 2 Digit)
100 V AC - 700 V AC	100 V AC - 700 V AC	1 V	± (2.5 % + 2 Digit)
0.0 V DC - 99.9 V DC	5.0 V DC - 99.9 V DC	0.1 V	± (2.5 % + 2 Digit)
100 V DC - 1000 V DC	100 V DC - 1000 V DC	1 V	± (2.5 % + 2 Digit)
Detection AC/DC	Yes (Automatic)		
+ / - polarity check	Yes		

AC/DC current with i100 clamp

Display range	Measuring range	Resolution	Accuracy (DC, AC 50 Hz/60 Hz)
0.0 A DC - 100 A DC	1.0 A DC - 100 A DC	0.1 A	± (5 % + 2 Digit) *
0.0 A AC - 100 A AC TRMS	1.0 A AC - 100 A AC TRMS		± (5 % + 2 Digit) *

* i100 clamp tolerances not inclusive

i100 Clamp Tolerances

Display range	Measuring range	Output signal	Accuracy (DC, AC 50 Hz/60 Hz)
N/A	1 A - 100 A DC or AC < 1 kHz	10 mV/A AC/DC	± (1.5 % + 0.1 A)

AC/DC Power measurement (with i100 clamp)

Display range	Measuring range	Resolution	Accuracy (DC, AC 50 Hz/60 Hz)
0.0 V AC - 700 V AC 0.0 V DC - 1000 V DC	5.0 V AC - 700 V AC 5.0 V DC - 1000 V DC	0.1 V	± (2.5 % + 2 Digit)
0 A AC/DC - 100 A AC/DC	1 A AC/DC - 100 A AC/DC	0.1 A	± (6.5 % + 3 Digit)
0 kW/kVA - 100 kW/kVA	5 kW/kVA - 100 kW/kVA	1 kW/kVA	± (10 % + 4 Digit)

Product specifications

SMFT-1000 PV Tester, and Performance Analyze, I-V Curve Tracer	
SMFT-1000 size	10 cm x 25.0 cm x 12.5 cm (3.8 in x 9.8 in x 4.9 in)
SMFT-1000 weight	1.4 kg (3.09 lb)
Battery	6 AA IEC LR6
Operating temperature	0 °C to 50 °C (32 °F to 122 °F)
Storage temperature	-30 °C to 60 °C (-22 °F to 140 °F) batteries removed
Operating altitude	up to 2000 m
Storage altitude	up to 2000 m
Safety	
SMFT-1000 PV Analyzer	IEC 61010-1 Pollution Degree 2 IEC 61010-2-034 CAT III 1000 V dc, CAT III 700 V AC
i100 Current Clamp	IEC 61010-2-032, Type D (for insulated conductors), 1000 V
Accessories	IEC 61010-031
TL 1000-MC4	CAT III 1500 V, 20 A
TP1000 Remote Probe (with cap)	CAT IV 600 V, CAT III 1000 V, 10 A
TP1000 Remote Probe (without cap)	CAT II 1000 V, 10 A
TL 1000 Test Leads	CAT III 1000 V, 10 A
TL 1000/30M Test Leads	CAT III 1000 V, CAT IV 600 V, 5 A (on reel) 10 A (fully extended)
TP74 Test Probes (with cap)	CAT III 1000 V, 10 A
TP74 Test Probes (without cap)	CAT II 1000 V, 10 A
AC285 Alligator Clip	CAT III 1000 V, 10 A
Performance	IEC 61557-1, IEC 61557-2, IEC 61557-4, IEC 61557-10
Electromagnetic Compatibility (EMC)	
International	IEC 61326-1: Portable Electromagnetic Environment, CISPR 11: Group 1, Class A Group 1: Equipment has intentionally generated and/or uses conductively-coupled radio frequency energy that is necessary for the internal function of the equipment itself. Class A: Equipment is suitable for use in all establishments other than domestic and those directly connected to a low-voltage power supply network that supplies buildings used for domestic purposes. There may be potential difficulties in ensuring electromagnetic compatibility in other environments due to conducted and radiated disturbances. Caution: This equipment is not intended for use in residential environments and may not provide adequate protection to radio reception in such environments.
Wireless Radio Module	
Frequency range	2.402 GHz to 2.480 GHz
Output power	8 dBm

Fluke Premium Care

Reduce unplanned expenses and get the most out of your tools

When you invest in the best equipment in the industry, you want your money to go as far as possible. Fluke Premium Care provides coverage above and beyond your tool's original product warranty, so you don't need to worry about unexpected downtime caused by damaged test equipment, accessories, or tools in need of calibration or repair.

Fluke Premium Care is available in both a Standard and Gold level with one-year or three-year plan options so you can choose the plan that is right for you.

Fluke Premium Care-Standard

- Provides additional protection for damage not covered by the original product warranty
- Annual performance check or traceable calibration
- Prepaid express freight to/from our lab
- Replacement of damaged accessories
- Product updates
- Priority technical support
- Expedited repair and service

Fluke Premium Care is not available in all countries.

Ordering information

Fluke SMFT-1000 Multifunction PV Analyzer

What's included

- Fluke SMFT-1000-BP Professional Tool Backpack
- SMFT-1000 Multifunction PV Analyzer
 - Carry strap
 - Fuse pack
 - Adapter Cable IRDA Optical-to-USB
 - Zero adapter
- IRR2-BT Wireless Solar Irradiance Meter Pro
 - 8OPR-IRR External Temperature Probe
 - Mounting Bracket for solar panel
 - Carry Case
- i100 AC/DC Current Clamp 100 A
 - TPAK Magnet Set
- TP1000 Test Probe with Remote Test Button
- TL1000 Test Lead Set
 - TL1000-MC4 Test Lead Set
 - TL1000/30M Test Lead on Reel
 - Coupler set
 - (6) AA Batteries

The SMFT-1000 is compatible with the Fluke portfolio of test and measurement tools and is an integral part of your total PV system testing solution.

Also available as a kit with Advanced TruTest™ Software and MC4 Solar Clamp Test Lead Set SMFT-1000/KIT

Recommended tools for use with the SMFT-1000

- TruTest™ Data Management and Reporting Software
- 393 FC CAT III 1500 V Solar Clamp Meter
- 87V MAX True-rms Digital Multimeter
- 1587 FC Insulation Multimeter
- Ti480 PRO Infrared Camera
- 1625-2 GEO Earth Ground Tester
- 500 Series Battery Analyzers
- Pomona PVLEAD3 MC4 Solar Clamp Test Lead Set



Fluke. *Keeping your world up and running.*

©2022 Fluke Corporation.
Specifications subject to change without notice.
8/2022 220566-en

Modification of this document is not permitted without written permission from Fluke Corporation.


Fluke Premium Care

Coverage that prevents unexpected downtime caused by damaged test equipment, accessories, or tools in need of calibration or repair.



Accidental damage and repair

Avoid costly repairs and rest easy knowing that any damage to your test tool is covered



Replacement of damaged accessories

Replace damaged accessories that could be affecting the accuracy of your test results at no extra cost



Annual tool inspection and calibration

Ensure your test tool is providing accurate results and adheres to regulatory compliance by leaving it in the hands of our experts









Expedited calibration and repair

Skip the wait - your calibration or repair will be expedited so you can get back to your tool and work faster

	Standard warranty	Premium Care
Repair manufacturing defects	•	•
Annual calibration or performance test		•
Accidental damage and repair of main unit		•
Expedited calibration and repair		•
Expedited freight		•
Replacement or repair of damaged accessories		•
Priority Tech Support		•

Potential cost savings

Contact your local Fluke dealer representative to obtain a quote for your specific products.

Product covered	Potential cost without Premium Care*	Cost with Premium Care 1-year Standard plan*
 ii910 Precision Acoustic Imager		
 ii900 Industrial Acoustic Imager		
 1770 Series Power Quality Analyzers		
 MDA Series Motor Drive Analyzers		
 190 Series ScopeMeter™ Portable Oscilloscope		
 SMFT-1000 Multifunction PV Tester and Performance Analyzer, I-V Curve Tracer		

*Costs are approximated as price varies depending on model, accessory, shipping location, etc.

In case of Fluke Premium Care 3-year, the cost savings will be even higher; approx. 10%.

Fluke Premium Care support plans selection chart

Description	Choose your Fluke Premium Care		
	1-year	3-year	
Acoustic imagers	Fluke Premium Care for: Fluke ii900 Industrial Acoustic Imager	FPC1S-II900-1	FPC3S-II900-1
	Fluke Premium Care for: Fluke ii910 Precision Acoustic Imager	FPC1S-II910-1	FPC3S-II910-1
	Fluke ii900 Industrial Acoustic Imager with Fluke Premium Care Bundle	FLUKE-II900/FPC EU	-
	Fluke ii910 Precision Acoustic Imager with Fluke Premium Care Bundle	FLUKE-II910/FPC EU	-
PQ analyzers	Fluke Premium Care for: Fluke 1770 Series Power Quality Analyzers (1773, 1775, 1777)	FPC1S-FPQ170-1	FPC3S-FPQ170-1
	Fluke 1775 Power Quality Analyzer with Fluke Premium Care Bundle	FLUKE-1775/FPC EU	-
	Fluke 1777 Power Quality Analyzer with Fluke Premium Care Bundle	FLUKE-1777/FPC EU	-
Motor drive analyzers	Fluke Premium Care for: MDA-550 Motor Drive Analyzer	FPC1S-MDA-500-1	FPC3S-MDA-500-1
	Fluke MDA-550 Motor Drive Analyzer with Fluke Premium Care Bundle	FLUKE-MDA-550/PFC EU	-
Scope meters	Fluke Premium Care for: Fluke ScopeMeter 190 Series III (190-062, 190-102, 190-104, 190-202, 190-204, 190-502, 190-504)	FPC1S-SCM190-1	FPC3S-SCM190-1
	Fluke 190-504-III ScopeMeter Test Tool with Fluke Premium Care Bundle	FLUKE-190-504/FPC EU	-
Multifunction PV Tester	Fluke Premium Care for: Fluke SMFT-1000 Kit Multifunction PV Tester and Performance Analyzer	FPC1S-SMFT-1000-1	FPC3S-SMFT-1000-3
	Fluke SMFT-1000 Multifunction PV Tester and Performance Analyzer with Fluke Premium Care Bundle	SMFT-1000/FPC EU	-