




Part Number : [2244831022](#)

Product Description : MicroTPA-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 150.00mm Length, 2 Circuits, Natural

Series Number : 224483

Status : Active

Product Category : Power and Signal Cable Assemblies




Documents & Resources

Drawings

[Drawing 2244831022_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224483
Description	MicroTPA-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 150.00mm Length, 2 Circuits, Natural
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	MicroTPA-to-Pigtail
Product Family	MicroTPA Connector System
Product Name	MicroTPA
Type	Discrete Wire Assembly
UPC	196823368622

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	2
Color - Resin	Natural
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.587/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag

Pitch - Mating Interface	2.00mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Insulation Diameter	1.22mm
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroTPA Plug Housings	<u>51227</u>
MicroTPA Vertical High Wall Type Headers	<u>55487</u>
MicroTPA Vertical Kinked PC Tail Headers	<u>55755</u>