



Part Number : [313872033](#)

Product Description : 2.54mm Pitch, MX123 Header, 73 Circuits Shrouded Assembly, Qty(72) 0.64mm Square Signal Pins + Qty(1) 2.8mm Power Blade, Harness Side Key Code C, Blue (Ag Mate Side Finish)

Series Number : 31387

Status : Active

Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[Drawing 313872033_sd.pdf](#)

[Packaging Design Drawing PK-31301-916-001.pdf](#)

3D Models and Design Files

[3D Model 313872033_stp.zip](#)

Specifications

[Application Specification AS-31386-200-001.pdf](#)

[Product Specification PS-31387-200-001.pdf](#)

[Test Summary TS-31387-1658-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	31387
Description	2.54mm Pitch, MX123 Header, 73 Circuits Shrouded Assembly, Qty(72) 0.64mm Square Signal Pins + Qty(1) 2.8mm Power Blade, Harness Side Key Code C, Blue (Ag Mate Side Finish)
Application	Automotive, Power, Wire-to-Board
Component Type	PCB Header
Product Family	MX123 Sealed Connection System
Product Name	MX123
UPC	887191473673

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	73
Circuits (maximum)	73
Color - Resin	Blue
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes

Lock to Mating Part	Yes
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	23.220/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Carton
PC Tail Length	6.50mm
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX123 Receptacle Housings	<u>34566</u>

Use with Part(s)

Description	Part Number
MX64 Female Terminals	<u>34736</u>