





Features

RoHS Compliant

- Input voltage range up to 8:1
- High efficiency up to 92%
- No-load input current as low as 0.5mA
- Operating ambient temperature range: -40°C to +85°C
- · Output short-circuit protection
- · Meet MIL-STD-810F vibration test

Selection Guide

Part Number	Input Voltage (V DC)*	Out	Efficiency (%)		Capacitive Load		
Fait Number	Nominal	Voltage	Current	MIN./Typ.		(μF) - Max.	
	(Range)	(V DC)	(mA) Max.	Vin=24V	Vin=48V	IVIAX.	
MP-K78Ux6-1000R3	48	6.5	1000	82/86	81/85	1200	
MP-K78Ux6-1000R3L	(9-75)	0.5	1000	02/00	01/00	1200	

Note: *For input voltage exceeding 60V DC, an input capacitor of 100uF/100V is required.

Input Specifications

Item	Operating Conditions	Min.	Тур.	Max.	Unit
No-load Input Current	Nominal input voltage	-	0.5	1.5	mA
Reverse Polarity at Input	-	A۱	oid / No	ot protec	ted
Input Filter	-		Capacit	ance filte	er

Output Specifications

Item	Operating	Conditions	Min.	Тур.	Max.	Unit
Voltage Accuracy	10%-100%, input voltage range		-	±1.5	±2.5	
Linear Regulation	Full load, input voltage range		-	±0.6	±1.5	%
Load Regulation	Nominal input voltage, 10% -	100% load	-	±0.6	±1	
Ripple & Noise*	20MHz bandwidth, nominal input voltage, 10% -100% load		-	75	-	mVp-p
Temperature Coefficient	Operating temperature -40°C to +105°C		-	-	±0.02	%/°C
Transient Response Deviation	Nominal input voltage, 25% load step change		-	±100	±180	mV
Transient Recovery Time			-	150	250	μs
Short-circuit Protection	Input voltage range	nput voltage range Ambient temperature≤85°C C Ambient temperature>85°C		tinuous,	self-rec	overy
Short-circuit Protection	I input voitage range			Short≤3s		

Notes:

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



^{*}The "parallel cable" method is used for ripple and noise test, refer to DC-DC Converter Application Notes for specific information.



General Specifications

Item	Operating Conditions	Min.	Тур.	Max.	Unit
Operating Temperature	-	-40	-	+105	
Storage Temperature	Product	-55	-	+125	
Storage Temperature	Tag	-40		+300	°C
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds	-	-	+300	
Storage Humidity	Non-condensing	5	-	95	%RH
Vibration*	Bottom-filled silicone rubber		MIL-S	ΓD-810F	
Switching Frequency	Full load, nominal input voltage	-	250	-	kHz
МТВБ	MIL-HDBK-217F@25°C	8215	-	-	k hours


Note: * Meeting the vibration standard requires filling the bottom void of the product with silicone rubber.

Mechanical Specifications


Case Material		Black plastic; flame-retardant and heat-resistant (UL94V-0)
Dimensions	MP-K78U24-700R3	12.1mm × 8.6mm × 17.5mm
Dimensions	MP-K78U24-700R3L	20.35mm × 12.1mm × 8.6mm
Moight	MP-K78U24-700R3	6.2g (Typ.)
Weight	MP-K78U24-700R3L	6.6g (Typ.)
Cooling Method		Free Air Convection


Typical Characteristic Curves

Temperature Derating Curves




multicomp PRO





Design Reference

Typical application




Part Number	C1 (Ceramic Capacitor)	C2 (Ceramic Capacitor)
MP-K78Ux6-1000R3	10E/100\/	22 [/40./
MP-K78Ux6-1000R3L	10μF/100V	22µF/10V

Notes:

- 1. The required C1 and C2 capacitors must be connected as close as possible to the terminals of the module;
- 2. Refer to Table 1 for C1 and C2 capacitor values. For certain applications, increased values and/or tantalum or low ESR electrolytic capacitors may also be used instead;
- 3. Converter cannot be used for hot swap and with output in parallel.

EMC compliance circuit



C4/C5	C1/C2/C3	C6	LDM1	LDM2
680µF/100V	4.7µF/100V	10μF/50V	10μH	22µH

PCB Heat Dissipation Copper Foil Recommended


Series	Heat dissipation copper foil layer	Heat dissipation copper foil area
MP-K78UXX-1000R3	double	15mm×15mm
MP-K78UXX-1000R3L	single	20mm×20mm

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro





Diagram MP-K78U24-700R3




Pin-Out			
Pin	Mark		
1	+Vin		
2	GND		
3	+Vout		
4	Case Pin		
5	Case Pin		

Note:

PIN4 and PIN5 are shell terminals for heat dissipation. When using the product, connect the terminals to the rear PCB board, and the PCB must be suspended.

MP-K78U24-700R3L



Pin-Out		
Pin	Mark	
1	+Vin	
2	GND	
3	+Vout	
4	Case Pin	

Note: PIN4 is the shell terminal, which dissipates heat. When using the product, connect the terminal to the rear PCB board. The PCB must be suspended in the air.

Dimensions: Millimetres (Inches)

Pin Diameter Tolerances: ±0.1mm (±0.004") General Tolerances: ±0.5mm (±0.02")

Part Number Table

Description	Part Number
Non Isolated Board Mount, DC / DC Converters, 6.5V, 1A	MP-K78Ux6-1000R3
Non Isolated Board Mount, DC / DC Converters, 6.5V, 1A	MP-K78Ux6-1000R3L

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

