


## Product information

# 79 22 125

## Precision Electronics Diagonal Cutter

DIN ISO 9654



- Round head
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened




### General

Article No.	79 22 125
EAN	4003773061342
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	60 g
Dimensions	125 x 60 x 19 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities soft wire (diameter)	Ø 0.1 – 1.7 mm
Jaw length (B)	10 mm
Jaw thickness (joint) (D)	6.5 mm
Head width (A)	11 mm





**Accessories**

00 11 V79

Material catcher for 79 02 / 22 125 ESD,

*technical change and errors excepted*